

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301510019](#)
Status: **Active**
Overview: [Heavy-Duty Industrial Wiring Devices](#)
Description: Super-Safeway Adapter NEMA L5-15R Receptacle - Female End 15A/125V, Non-NEMA Plug - Male End, 15A/125V

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family [Wiring Devices](#)
 Series [130151](#)
 IP Rating IP67
 NEMA Configuration [NEMA L5-15](#)
 Overview [Heavy-Duty Industrial Wiring Devices](#)
 Product Name Super-Safeway
 Receptacle Type N/A
 Specialty N/A
 Taxonomy [Wiring Devices](#)
 Type Adapter
 UPC 78678875019

Physical

Flange No
 Flip Lid No
 Gender Male-Female
 Length N/A
 Locking Blade Yes
 Poles 2-pole/3-wire

Electrical

Cord Type N/A
 Current - Maximum per Contact 50.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 125V

Material Info

Engineering Number 1725



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130151 Series](#)