


1 - 6437138 - 3 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



FLEXSTRIP® Jumpers

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? 2.54 mm Centerline
- ? Nomex Insulation Material
- ? Insulation Length = 40.64 mm
- ? Pin Arrangement (Left) = A
- ? Pin Arrangement (Right) = A

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling Product Feature Selector](#)
- [Contact Us About This Product](#)

1 - 6437138 - 3

[Active](#)

Documentation & Additional Information

Product Drawings:

? [None Available](#)

Catalog Pages/Data Sheets:

? [None Available](#)

Product Specifications:

? [None Available](#)

Application Specifications:

? [None Available](#)

Instruction Sheets:

? [None Available](#)

CAD Files:

? [None Available](#)

Additional Information:

? [Product Line Information](#)

Additional Product Images:

- ? [Product View](#)
- ? [Product View](#)

Related Products:

? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Insulation Material](#) = Nomex
- ? [Number of Conductors](#) = 16

Electrical Characteristics:

- ? Current Rating (Amps.) = 3
- ? Impedance (?) = 107
- ? Voltage Rating (VAC) = 300

Body Related Features:

- ? [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]
- ? [Insulation Length \(mm \[in\]\)](#) = 40.64 [1.600]

Configuration Related Features:

- ? [Pin Arrangement \(Left\)](#) = A
- ? [Pin Arrangement \(Right\)](#) = A

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? Operating Temperature (°C [°F]) = -40 - +125 [-40 - +257]

Other:

- ? Brand = Tyco Electronics