

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1727186111](#)
Status: **Active**
Overview:
Description: Mini-Fit TPA2/Sigma Female Crimp Terminal, Phosphor Bronze, Pre-Plated Tin (Sn), 22-24 AWG, 1.65-2.38mm Insulation Diameter, Reel

General

Product Family	Crimp Terminals
Series	172718
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	See product specification for current derating information; See Mini-Fit TPA2 housing series for 3D models.
Crimp Quality Equipment	Yes
Overview	minifit_power_connector_solutions
Packaging Alternative	1727186112 (Bag)
Product Name	Mini-Fit Sigma, Mini-Fit TPA2
Taxonomy	Crimp Terminals
UPC	889056179355

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.210/g
Packaging Type	Reel
Plating min - Mating	2.500µm
Plating min - Termination	2.500µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.65-2.38mm
Wire Size AWG	22, 24
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	11.0A
Voltage - Maximum	600V AC/DC

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-172718-0000-001
Application Tooling Documents	ATS-2002180200-001, ATS-2002181200-001, ATS-639037000-001
Packaging Specification	PK-172718-0000-000, PK-172718-0001-000
Product Specification	PS-172718-0000-001
Sales Drawing	SD-172718-0000-000
Test Summary	1727180001-TS-000, 1727180002-TS-000, 2131370001-TS-000, 2131370002-TS-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[172718](#) Series

Use With

Mini-Fit TPA2/Sigma Receptacle Housings
[172708](#) , [200453](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Hand Crimp Tool for Mini-Fit TPA2 Male and Female Crimp Terminals, 22 AWG, Large and Small Insulation Grips	2002180200
Hand Crimp Tool for Mini-Fit TPA2 Male and Female Crimp Terminals, 24 AWG, Large and Small Insulation Grips	2002181200
Extraction Tool for Mini-Fit TPA2 Crimp Terminal, 16-24 AWG	638246210
FineAdjust Applicator for Mini-Fit TPA2 Crimp Terminals, 0.22mm ² , 0.25mm ² , 0.35 mm ² and 22-24 AWG wires	639037000

This document was generated on 10/18/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION