

Product Details for 1 -1337432 -0



1 -1337432 -0

[Active](#)

BNC RF Connectors

[RoHS Compliant](#) (Statement of Compliance)

Product Highlights:

- ? Connector
- ? Connector Type = BNC
- ? Plug
- ? Terminate To Coaxial Cable
- ? Not Stacked

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [BNC STRAIGHT PLUG CRIMP 75 OHM RG179B/U, 187A/U, URM111](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Connector Type](#) = BNC
- ? [Gender](#) = Plug
- ? [Stacked](#) = No
- ? [Number of Ports](#) = 1
- ? [Crimp Type](#) = Hex
- ? [Body Style](#) = Straight
- ? [Grade](#) = Professional
- ? [Body Material](#) = Brass
- ? [Sealed](#) = No
- ? [Isolated](#) = No
- ? [Dielectric Material](#) = PTFE
- ? [Coupling Nut Material](#) = Brass
- ? Gasket Material = White Silicone Rubber

Mechanical Attachment:

- ? Surface Mountable = No
- ? Panel Attachment = Without

Electrical Characteristics:

- ? [Connector Impedance \(?\)](#) = 75
- ? Frequency = DC to 2 GHz

Termination Related Features:

- ? [Coaxial Cable Termination Type](#) = Crimp

Body Related Features:

- ? [Hardware Included](#) = No
- ? [Body Plating](#) = Silver
- ? [Polarized](#) = No
- ? Ferrule Type = Hex
- ? Hand Tool No. = 9 -1478240 -0
- ? Interchangeable Die Set Number = 9 -1478245 -0
- ? Crimp Dimensions = 1.75 + 4.75

Contact Related Features:

- ? [Center Contact Material](#) = Brass
- ? [Center Contact Plating](#) = Silver

Configuration Related Features:

- ? [Coaxial Cable Type \(RG/U or Mfg.\)](#) = 179B/U, 187A/U, Raychem 7530A1314, Raychem 7530H1444, Raychem CLFH -179, Raychem EPD 46504R, URM 111

Industry Standards:

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Converted to comply with RoHS directive

Conditions for Usage:

- ? [Terminate To](#) = Coaxial Cable
- ? Operating Temperature (Max.) (°C) = 165

Packaging Related Features:

- ? Packaging Method = Individual
- ? Packaging Quantity = 50

Other:

- ? Brand = Greenpar