

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2023960407](#)  
**Status:** **Active**  
**Overview:** Pico-Clasp Wire-to-Board Connectors  
**Description:** 1.00mm Pitch, Pico-Clasp PCB Header, Single Row, Right-Angle, Surface Mount, 0.10µm Gold Plated, Friction Lock, 4 Circuits, Natural

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification 5013301000-PS-JAP-002 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Application Specification 5013300000-AS-000 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Packaging Specification 2023969200-200 (PDF)</a>
<a href="#">Product Specification 5013300000-PS-002 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification 5013301000-PS-002 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification 5013301000-PS-CHI-002 (PDF)</a>	

**General**

Product Family	PCB Headers
Series	<a href="#">202396</a>
Application	Signal, Wire-to-Board
Overview	<a href="#">Pico-Clasp Wire-to-Board Connectors</a>
Product Name	Pico-Clasp
Taxonomy	PCB Headers and Receptacles
UPC	889056815376

**Physical**

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Nylon
Net Weight	109.500/mg
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Plating min - Mating	0.100µm
Plating min - Termination	0.051µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

**Electrical**

Current - Maximum per Contact	1.5A
Voltage - Maximum	100V AC (RMS)/DC



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[202396 Series](#)

**Mates With**

[Pico-Clasp Female Housing 501330](#)

**Material Info**

**Reference - Drawing Numbers**

Application Specification	5013300000-AS-000
Packaging Specification	2023969200-200
Product Specification	5013300000-PS-002, 5013301000-PS-002, 5013301000-PS-CHI-002, 5013301000-PS-JAP-002
Sales Drawing	2023960000-SD-000

This document was generated on 10/18/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**