

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2032630001](#)
Status: **Active**
Overview: [Sentrality Pin and Socket Interconnect System](#)
Description: [Sentrality 8.00mm Knurled Press-fit Pin in Bag, 26.00mm Engagement Length](#)

Documents:

3D Model	Packaging Specification 2032630006-PK-000 (PDF)
Drawing (PDF)	Test Summary 2043130008-TS-000 (PDF)
3D Model (PDF)	Test Summary 2043131234-TS-000 (PDF)
Product Specification 2043130001-PS-000 (PDF)	Datasheet (PDF)
Application Specification 2043130001-AS-000 (PDF)	RoHS Certificate of Compliance (PDF)



Series image - Reference only

General

Product Family	PCB Headers
Series	203263
Application	Board-to-Board, Busbar-to-Board, Busbar-to-Busbar, Power
Overview	Sentrality Pin and Socket Interconnect System
Product Name	Sentrality
Taxonomy	PCB Headers and Receptacles
UPC	191128426985

Physical

Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	8.00mm
Durability (mating cycles max)	200
Glow-Wire Capable	No
Height Above Board	26.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Net Weight	13.087/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Temperature Range - Operating	-40° to +125°C
Termination Interface: Style	Press-Fit

Electrical

Current - Maximum per Contact	200.0A
Voltage - Maximum	600V

Material Info

Reference - Drawing Numbers

Application Specification	2043130001-AS-000
Packaging Specification	2032630006-PK-000
Product Specification	2043130001-PS-000
Sales Drawing	2032630001-SD-000
Test Summary	2043130008-TS-000, 2043131234-TS-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[203263](#) Series

Mates With

8.00mm Surface Mount Sockets [204365](#) ,
[204318](#) . 8.00mm Press-Fit Sockets [204313](#)
, [204316](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION