

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2032630034](#)  
**Status:** **Active**  
**Overview:** [Sentrality Pin and Socket Interconnect System](#)  
**Description:** [Sentrality 3.40mm Knurled Press-fit Pin in Bag, 26.00mm Engagement Length](#)

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification 2032630006-PK-000 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Test Summary 2043131234-TS-000 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification 2043130018-PS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification 2043130018-AS-000 (PDF)</a>	



**General**

Product Family	PCB Headers
Series	<a href="#">203263</a>
Application	Board-to-Board, Busbar-to-Board, Busbar-to-Busbar, Power
Overview	<a href="#">Sentrality Pin and Socket Interconnect System</a>
Product Name	Sentrality
Taxonomy	PCB Headers and Receptacles
UPC	191130073702

**Physical**

Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	3.40mm
Durability (mating cycles max)	200
Glow-Wire Capable	No
Height Above Board	26.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Net Weight	2.527/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Temperature Range - Operating	-40° to +125°C
Termination Interface: Style	Press-Fit

**Electrical**

Current - Maximum per Contact	75.0A
Voltage - Maximum	600V

**Material Info**

**Reference - Drawing Numbers**

Application Specification	2043130018-AS-000
Packaging Specification	2032630006-PK-000
Product Specification	2043130018-PS-000
Sales Drawing	2032630034-SD-000
Test Summary	2043131234-TS-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[203263](#) Series

**Mates With**

3.40mm Surface Mount Sockets [204365](#) ,  
[204318](#) . 3.40mm Press-Fit Sockets [204313](#)  
, [204316](#)

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**