

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2078450003](#)
Status: **Active**
Overview: [KK Interconnect Systems](#)
Description: [KK Plus 250 Terminal Position Assurance \(TPA\) Retainer, 3 Circuits, Natural](#)

Documents:

3D Model	Product Specification 2079020001-PS-SK-000 (PDF)
Drawing (PDF)	Application Specification 2079020001-AS-000 (PDF)
3D Model (PDF)	Packaging Specification 2078450000-PK-000 (PDF)
Product Specification 2079020001-PS-000 (PDF)	Test Summary 2079020000-TS-000 (PDF)
Product Specification 2079020001-PS-CH-000 (PDF)	Datasheet (PDF)
Product Specification 2079020001-PS-ES-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 2079020001-PS-JP-000 (PDF)	

Agency Certification

CSA	152514
-----	--------

General

Product Family	Accessories
Series	207845
Component Type	Terminal Position Assurance
Overview	KK Interconnect Systems
Product Name	KK Plus
Taxonomy	Connector Accessories
UPC	191130124015

Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Natural
Flammability	94V-0
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.062/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	2079020001-AS-000
Packaging Specification	2078450000-PK-000
Product Specification	2079020001-PS-000, 2079020001-PS-CH-000, 2079020001-PS-ES-000, 2079020001-PS-JP-000, 2079020001-PS-SK-000
Sales Drawing	2078450004-SD-000
Test Summary	2079020000-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[207845 Series](#)

Use With

[KK Plus 250 Receptacle Housing](#)
[2078410003](#)