

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2078450007](#)
Status: **Active**
Overview: [KK Interconnect Systems](#)
Description: [KK Plus 250 Terminal Position Assurance \(TPA\) Retainer, 7 Circuits, Natural](#)

Documents:

3D Model	Product Specification 2079020001-PS-SK-000 (PDF)
3D Model (PDF)	Application Specification 2079020001-AS-000 (PDF)
Drawing (PDF)	Packaging Specification 2078450000-PK-000 (PDF)
Product Specification 2079020001-PS-000 (PDF)	Test Summary 2079020000-TS-000 (PDF)
Product Specification 2079020001-PS-CH-000 (PDF)	Datasheet (PDF)
Product Specification 2079020001-PS-ES-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 2079020001-PS-JP-000 (PDF)	

Agency Certification

CSA 152514

General

Product Family [Accessories](#)
 Series [207845](#)
 Component Type [Terminal Position Assurance](#)
 Overview [KK Interconnect Systems](#)
 Product Name [KK Plus](#)
 Taxonomy [Connector Accessories](#)
 UPC [191130124053](#)

Physical

Circuits (Loaded) 7
 Circuits (maximum) 7
 Color - Resin [Natural](#)
 Flammability [94V-0](#)
 Lock to Mating Part [Yes](#)
 Material - Resin [Nylon](#)
 Net Weight [0.109/g](#)
 Number of Rows [1](#)
 Packaging Type [Bag](#)
 Temperature Range - Operating [-40° to +105°C](#)

Material Info

Reference - Drawing Numbers

Application Specification [2079020001-AS-000](#)
 Packaging Specification [2078450000-PK-000](#)
 Product Specification [2079020001-PS-000, 2079020001-PS-CH-000, 2079020001-PS-ES-000, 2079020001-PS-JP-000, 2079020001-PS-SK-000](#)
 Sales Drawing [2078450004-SD-000](#)
 Test Summary [2079020000-TS-000](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2022)4187-DC (10
 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[207845 Series](#)

Use With

[KK Plus 250 Receptacle Housing
 2078410007](#)