

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200668821](#)
Status: **Active**
Overview: Brad® M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable (European Market)
Description: Micro-Change® (M12) Double-Ended Cordset with Knurled Hexnut, 4 Poles, Female (Straight) to Male (Straight), 22 AWG, Unshielded WSOR Cable, 5.0m (16.40') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification TS-120065-001-001 \(PDF\)](#)



General

Product Family	Industrial Cordsets
Series	120066
Connector End A	Micro-Change® (M12)
Connector End B	Micro-Change® (M12)
IP Rating	IP67
Material - Contact	Brass
Overview	Brad® M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable (European Market)
Product Name	Micro-Change® (M12)
Region	Europe
Type	Double Ended
UPC	887191555133

Physical

Cable Diameter	5.10mm (.201")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-25°C to +85°C
Wire Size AWG	22
Wire/Cable Type	WSOR

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V

Material Info

Engineering Number	884030B30M050
--------------------	---------------

Reference - Drawing Numbers

Product Specification	TS-120065-001-001
Sales Drawing	1200659548-00P, 1200668993-000

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[120066 Series](#)