

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200680194](#)  
**Status:** **Active**  
**Overview:** Brad® Micro-Change® Connectors  
**Description:** Micro-Change® (M12) In-Line Splitter, 4 Pole, 1 x 4-Pole Male (Straight) to 2 x 3-Pole Female (Straight), 22 AWG TPE Cable, 0.30m Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E152210

**General**

Product Family Industrial Tees and Splitters  
 Series [120068](#)  
 IP Rating IP67  
 Overview [Brad® Micro-Change® Connectors](#)  
 Product Name Micro-Change® (M12)  
 Type Splitter - In-line  
 UPC 78678852731

**Physical**

Color - Cable Jacket Yellow  
 Drop Connector Micro-Change® (M12)  
 Drop Gender Male  
 Keyway Single  
 LED Indicator No  
 Left Trunk Connector Micro-Change® (M12)  
 Left Trunk Gender Female  
 Leg 1 Length 4.0m  
 Leg 2 Length 4.0m  
 Material - Cable Jacket TPE  
 Material - Connector Body TPE  
 Material - Coupling Nut Nickel-plated Brass  
 Poles 3 Female/4 Male  
 Right Trunk Connector Micro-Change® (M12)  
 Right Trunk Gender Female  
 Temperature Range - Operating -30°C TO +80°C

**Electrical**

Current - Maximum per Contact 4.0A  
 Voltage - Maximum 250V AC/DC

**Material Info**

Engineering Number 884A30K03M040

**Reference - Drawing Numbers**

Sales Drawing SD-120068-022



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[120068](#) Series