

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5016471100](#)
Status: **Active**
Overview: iGrid Wire-to-Board Dual-Row System
Description: 2.00mm Pitch, iGrid Female Crimp Terminal, Tin (Sn) Plating, 22-26 AWG, Bag

Documents:

3D Model (PDF)	Application Specification 5016460000-A00 (PDF)
3D Model	Application Specification 5016460000-A01 (PDF)
Drawing (PDF)	Packaging Specification 5016479200-200 (PDF)
Product Specification 5016461001-PS-001 (PDF)	Datasheet (PDF)
Product Specification PS-501646-001-001 (PDF)	RoHS Certificate of Compliance (PDF)



Series image - Reference only

General

Product Family	Crimp Terminals
Series	501647
Application	Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	iGrid Wire-to-Board Dual-Row System
Packaging Alternative	5016471000 (Reel)
Product Name	iGrid
Taxonomy	Crimp Terminals
UPC	822350087292

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	76.000/mg
Packaging Type	Bag
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.95-1.50mm
Wire Size AWG	22, 24, 26
Wire Size mm ²	0.126-0.34

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	5016460000-A00, 5016460000-A01
Crimp Specification	5016470000-CS-000
Packaging Specification	5016479200-200
Product Specification	5016461001-PS-001, PS-501646-001-001
Sales Drawing	5016470000-SD-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

501647 Series

Use With

iGrid Receptacle Housing [501646](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool for MX150L, MX150, PT Bulb Socket, iGrid, SPOX, and Wire-to- Motor Terminals PremiumGrade Hand Crimp Tool for iGrid Female Terminals, 22-26 AWG and 0.30-0.20mm ² Wire	638131500 638192300
--	--

This document was generated on 10/14/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION