

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5025840260](#)
Status: **Active**
Overview: CLIK-Mate Wire-to-Board Connectors
Description: 1.50mm Pitch, CLIK-Mate PCB Receptacle, Single Row, Surface Mount, Tin Plating, Positive Lock, with Pick-and-Place Polyimide Tape, 2 Circuits, Beige

Documents:

| | |
|---|---|
| 3D Model (PDF) | Product Specification 5025781000-PS-CHI-000 (PDF) |
| 3D Model | Product Specification 5025781000-PS-JAP-000 (PDF) |
| Drawing (PDF) | Application Specification AS-502578-001-001 (PDF) |
| Product Specification 5025780000-PS-000 (PDF) | Packaging Specification SPK-502584-001-001 (PDF) |
| Product Specification 5025781000-PS-000 (PDF) | RoHS Certificate of Compliance (PDF) |

General

| | |
|----------------|--|
| Product Family | PCB Receptacles |
| Series | 502584 |
| Application | Signal, Wire-to-Board |
| Overview | CLIK-Mate Wire-to-Board Connectors |
| Product Name | CLIK-Mate |
| Taxonomy | PCB Headers and Receptacles |
| UPC | 883906292102 |

Physical

| | |
|--------------------------------|-----------------------|
| Circuits (Loaded) | 2 |
| Circuits (maximum) | 2 |
| Color - Resin | Beige |
| Durability (mating cycles max) | 30 |
| Glow-Wire Capable | No |
| Guide to Mating Part | Yes |
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Mated Height | 9.70mm |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Tin |
| Net Weight | 399.547/mg |
| Number of Rows | 1 |
| Orientation | Vertical |
| PCB Locator | No |
| PCB Retention | Yes |
| Packaging Type | Embossed Tape on Reel |
| Pitch - Mating Interface | 1.50mm |
| Pitch - Termination Interface | 1.50mm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | No |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |
| Termination Interface: Style | Surface Mount |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 2.0A |
| Voltage - Maximum | 100V |

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|--------------------|
| Application Specification | AS-502578-001-001 |
| Packaging Specification | SPK-502584-001-001 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[502584](#) Series

Mates With

CLIK-Mate Housing [502578](#) . CLIK-Mate Cable Assembly [15135](#)

Product Specification

Sales Drawing

5025780000-PS-000, 5025781000-PS-000,
5025781000-PS-CHI-000, 5025781000-PS-JAP-000
5025840000-SD-000

This document was generated on 10/17/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION