

504566-2 Product Details

 [Live Product Chat](#)



504566-2

TE Part Number: 504566-2

 **Obsolete**

[Add to Part List](#)
[Contact Product Information Center](#)

FSMA Connectors

[Not EU RoHS or ELV Compliant](#) ([Find RoHS Compliant Alternates](#))

Product Highlights:

- Connector
- Connector Type = FSMA I (905 Style)
- Jacket Outer Diameter = 3.10 mm
- Fiber Size = 140 Micron
- Loose Piece

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Connector, OPTIMATE, FSMA, Brass or Stainless Steel ...](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- [OPTIMATE FSMA Fiber Optic Connector Types 905 and 906](#) (PDF, English)

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- [Connector Type](#) = FSMA I (905 Style)
- Body Material = Brass

Mechanical Attachment:

- Strain Relief Material = Thermoplastic Elastomer

Termination Related Features:

- [Fiber Size \(Micron\)](#) = 140
- Mode = Multimode

Body Related Features:

- [Jacket Outer Diameter \(mm \[in\]\)](#) = 3.10 [0.122]
- Assembly Length (mm [in]) = 71.42 [2.810]
- Ferrule Material = Stainless Steel
- Body Plating = Nickel
- Strain Relief Color = Black

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Packaging Related Features:

- [Packaging Method](#) = Loose Piece

Other:

- Brand = AMP