

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5055680971

Status:

Active

Overview:

Micro-Lock Plus Connector System

Description:

1.25mm Pitch, Micro-Lock Plus PCB Header, Single Row, Vertical, Surface Mount, Tin-Bismuth Plating, Positive Lock, 9 Circuits, with Pick-and-Place Polyimide Tape, Black



Series image - Reference only

- Documents:
- 3D Model

Application Specification 5055650000-AS-000 (PDF)
- Drawing (PDF)

Application Specification AS-505565-001-001 (PDF)
- 3D Model (PDF)

Packaging Specification 5055689200-200 (PDF)
- Product Specification 5055650000-000 (PDF)

Datasheet (PDF)
- Product Specification 5055651000-PS-000 (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification 5055651002-PS-000 (PDF)

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	505568
Application	Signal, Wire-to-Board
Overview	Micro-Lock Plus Connector System
Product Name	Micro-Lock Plus
Taxonomy	PCB Headers and Receptacles
UPC	889056556514
Physical	
Breakaway	No
Circuits (Loaded)	9
Circuits (maximum)	9
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin-Bismuth
Material - Plating Termination	Tin-Bismuth
Material - Resin	Polyamide
Net Weight	275.994/mg
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Plating min - Mating	1.000µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	Vacuum Pick-Up Tape
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2022)4187-DC (10

June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

505568 Series

Mates With

Micro-Lock Plus Receptacle Housing

505565

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	5055650000-AS-000, AS-505565-001-001
Packaging Specification	5055689200-200
Product Specification	5055650000-000, 5055651000-PS-000, 5055651002-PS-000
Sales Drawing	5055680000-SD-000

This document was generated on 10/25/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION