

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1122190001

Status:

Active

Overview:

Woodhead ArcArrest Connector System

Description:

Woodhead ArcArrest Receptacle, Switch-Rated, 30.0A, 125V AC, 1-Pole+Neutral
+Ground, Insulator Keying Position 7



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Brochure \(PDF\)](#)

Agency Certification	
UL	E145923
General	
Product Family	Wiring Devices
Series	112219
IP Rating	IP69K
NEMA Configuration	N/A
Overview	Woodhead ArcArrest Connector System
Product Name	ArcArrest
Receptacle Type	Single
Specialty	Switch-Rated
Type	Receptacle
UPC	78172557864
Wire Size AWG	8 to 12
Physical	
Flange	Yes
Flip Lid	Yes
Gender	Female
Length	87.16mm (3.431")
Locking Blade	N/A
Net Weight	85.650/g
Poles	1
Electrical	
Cord Type	N/A
Current - Maximum per Contact	30.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V AC
Material Info	
Engineering Number	ARC30FA01
Reference - Drawing Numbers	
Sales Drawing	1122190010-000

EU ELV

Not Relevant

EU RoHS

Not Reviewed

China RoHS

Not Reviewed

REACH SVHC

Contained Per -
ED/01/2018 (15
January 2018)
2,4-di-tert-butyl-6-(5-
chlorobenzotriazol-2-
yl)p

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

112219 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION