

55892-1 Product Details

 [Live Product Chat](#)


55892-1

TE Part Number: 55892-1

 [Active](#)
 [Add to Part List](#)

Splices - Closed Barrel

 [Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- Seal and Splice Kit
- Sealed
- Splice Type = Butt
- Butt Splice Type = Standard
- Uninsulated

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)



Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Seal and Splice Kit
- [Sealed](#) = Yes
- [Splice Type](#) = Butt
- [Insulation](#) = No
- Finish = None
- Color = None
- Comment = Kit includes 10 [12-10 AWG] splice, 15 [22-18 AWG] splice, 25 [16-14 AWG] splice, molded case and crimping tool.

Body Related Features:

- [Butt Splice Type](#) = Standard
- [Wire Range \(mm \[AWG\]\)](#) = 0.30-6.00² [22-10]

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- Packaging Method = Kit
- Packaging Quantity = 1

Other:

- Brand = AMP