


Shield Terminators



TE Part Number: 587725-000

✓ Active

 Add to Part List

 Always ELV Compliant (Statement of Compliance)

Product Highlights:

- Sealing = Splash Resistant
- Cable Temperature Rating = 125 °C
- Jacket Outer Diameter = 5.08 mm
- Shield O.D. (Min.) = 2.15 mm
- With Preinstalled Lead

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [Solder Sleeve Devices Shield Termination with Braid](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- Product Line Information

Related Products:

- Tooling

List all Documents

Product Features (Please use the Product Drawing for all design activity)

Mechanical Attachment:

- Inside Diameter (mm [in]) = 4.30 [0.170]

Body Related Features:

- Jacket Outer Diameter (mm [in]) = 5.08
[0.200]

Housing Related Features:

- Sealing = Splash Resistant
- Shield O.D. (Min.) (mm [in]) = 2.15 [0.085]
- Preinstalled Lead = With
- Preinstalled Lead Wire Size (mm² [AWG]) = Braid Strap 654 [CMA 654]
- MIL or NAS Specification (MIL-S-83519) (NAS 1747) = Yes
- Length (Max.) (mm [in]) = 16.50 [0.650]

Configuration Related Features:

- Temperature Indication System = With
- Temperature Indication System Type = Thermochromic

Industry Standards:

- RoHS/ELV Compliance = ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was ELV compliant

Conditions for Usage:

- Cable Temperature Rating (°C) = 125
- Operating Temperature (Max.) (°C) = 150

Other:

- Brand = Raychem