

6318644 -1 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



6318644 -1

✓ [Active](#)

Memory Sockets

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Fax Modem Socket
- ? Gold Flash Contact Mating Area Plating Material
- ? Number of Positions = 124
- ? .80 mm Centerline
- ? Stack Height = 4.00 mm

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [EMBOSS ASSY FAXMODEM SOCKET 124 POS](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? [AMP FAXMODEM CONNECTOR LEAD FREE VERSION PRODUCT SPEC](#) (PDF, English)

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [2D Drawing](#) (DXF, Version 0)
- ? [3D Model](#) (IGES, Version 0)
- ? [3D Model](#) (STEP, Version 0)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = Fax Modem Socket
- ? [Number of Positions](#) = 124
- ? [Module Orientation](#) = Right Angle

Termination Related Features:

- ? Solder Tail Contact Plating = Gold Flash

Body Related Features:

- ? [Centerline \(mm \[in\]\)](#) = 0.80 [0.031]
- ? [Number of Rows](#) = Dual
- ? [Ejector Location](#) = None
- ? [Number of Keys](#) = 1
- ? Latch Material = Stainless Steel
- ? Latch Plating = Tin

Contact Related Features:

- ? Contact Mating Area Plating Material = Gold Flash
- ? [Contact Mount](#) = Surface Mount
- ? Contact Material = Phosphor Bronze

Housing Related Features:

- ? Housing Material = Thermoplastic High Temperature
- ? Housing Color = Black
- ? Housing Flammability Rating = UL 94V -0

Configuration Related Features:

- ? Stack Height (mm [in]) = 4.00 [0.157]
- ? [Insertion Style](#) = Cam -In

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Reflow solder capable to 245°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- ? Packaging Method = Tape & Reel
- ? Packaging Quantity = 250

Other:

- ? Brand = AMP