

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



 Active

Always EU RoHS/ELV Compliant (Statement of Compliance)

- ? Z-DOK
- ? Mating Type = Receptacle
- ? 40 Pairs

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

[Z-DOK CONNECTOR ASSEMBLY, RECEPTACLE, ESD CONTACTS](#)
(PDF, English)

? None Available

[Z-DOK* and Z -DOK* + Connectors](#) (PDF, English)

[Z-DOK and Z -DOK + Connectors](#) (PDF, English)

? None Available

- ? 2D Drawing (DXF, Version A)
- ? 3D Model (IGES, Version A)
- ? 3D Model (STEP, Version A)

List all Documents

? Product Line Information

? Tooling

Product Type Features:

? Product Type = Z -DOK
 ? Mating Type = Receptacle
 ? Mount Angle = Right Angle
 ? PCB Mount Style = Thru Hole (SMT Compatible)

- ? Number of Pairs = 40
- ? Boardlock Material = Brass
- ? Boardlock Plating = Tin over Nickel

? Termination (Solder) Post Length (mm [in]) = 3.10 [0.122]

? Solder Tail Contact Plating = Tin over Nickel

PCB Retention Method = ESD Boardlocks

- ? Contact Mating Area Plating = Gold (30)
- ? Contact Material = Copper Alloy

? Housing Material = Polyester

? Housing Color = Natural

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

? Brand = Tyco Electronics