



+ CONNECTORS

RECTANGULAR CONTACT INSERTS



✓ Active

TE CONNECTIVITY (TE)
MTC100-JA1-S14

Raychem | MT1000 , MTC

697117-000
TE Internal Number: 697117-000
Alias ID: 6-1195471-4

Not EU RoHS Compliant
Not EU ELV Compliant

Contact Type Socket
Number of Positions 10
Connector & Contact Terminates To Wire & Cable

↓ PRODUCT DRAWING
English

↓ 3D PDF

DOCUMENTATION

Product Drawings

Wafer Assembly, Socket, A, Style 1 Inch, 10 Contacts, With Oval Entry For 20-26 AWG. Temperature Rating 125 Deg. C MTC100 Series

PDF
English

CAD Files

Customer View Model

3D_STP.ZIP
English

Customer View Model

2D_DXF.ZIP
English

3D PDF

PDF

3D

Customer View Model

3D_IGS.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector & Contact Terminates To Wire & Cable

Product Size 1

Shell Size 25.4 [1]

Product Type Contact Insert

Configuration Features

Number of Positions 10

Keying A

Body Features

Interfacial Seal Without

Color Black

Insert Type Environmental

Insert Style Socket

Module Material High Grade Polyarylene Thermoplastic

Rear Grommet Without

Material Copper Alloy

Contact Features

Contact Type Socket

Dimensions

Wire Range (AWG) 20 – 26

Operation/Application

For Use With Round Wire

Packaging Features

Packaging Quantity 1

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
