

7-1105301 -2 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



7-1105301 -2

[Active](#)

HTS Connectors and Accessories

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? HVT Series
- ? Contact
- ? Contact Type = Socket
- ? Female
- ? Wire Range = 5.00 -6.00² [10] mm [AWG]

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? None Available

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = Contact
- ? Gender = Female
- ? Termination Style = Crimp
- ? Comment = Use with HTS Series HVT inserts

Electrical Characteristics:

- ? Contact Resistance (m?) = 3

Body Related Features:

- ? Series = HVT
- ? Wire Range (mm [AWG]) = 5.00 -6.00² [10]
- ? Strip Length (mm [in]) = 8.00 [0.315]

Contact Related Features:

- ? Contact Type = Socket
- ? Contact Mating Area Plating = Hard Silver
- ? Contact Material = Brass

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- ? Packaging Method = Loose Piece
- ? Packaging Quantity = 50

Other:

- ? Brand = HTS