

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



Always EU RoHS/ELV Compliant (Statement of Compliance)

- ? Contact Type = Square Post
- ? Length = 11.25 mm
- ? Phosphor Bronze Contact Material
- ? Gold (30) Contact Mating Area Plating Material
- ? Loose Piece

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

- [POST, MOD II, .025 SQUARE, UNINSULATED, LOOSE PIECE](#)
(PDF, English)

? None Available

? None Available

[AMPMODU Mod I And II Posts](#) (PDF, English)

? None Available

? None Available

? Product Line Information

? Tooling

List all Documents

Product Type Features:

- ? With Insulation Support = No
? Comment = Uninsulated

? Solder Tail Contact Plating = Nickel

? Length (mm [in]) = 11.25 [0.443]

? Contact Type = Square Post
 ? Contact Material = Phosphor Bronze
 ? Contact Mating Area Plating Material = Gold
 (30)

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

? Packaging Method = Loose Piece

? Brand = AMP