

# Solderless Terminal Kits

## Nylon Insulated Ring Terminals



**300V AC 105°C (221°F)**

Revision: A

**molex**<sup>®</sup>  
one company ▶ a world of innovation

# Molex Part Number: **19413-0106 (KIT-MX11)**

- **Description: 180pc Nylon Insulated Ring Terminals**

**Non-UL Crimp Tool Included.**

**For UL Listing, use Crimp Tool: 64001-0100 (RHT-1990) \*\*Not Included\*\***



# Molex Part Number: 19413-0106 (KIT-MX11)

Terminal Part Number	Description	Image
<b>19057-0005</b> (A-520-06)	<b>Ring Terminal, 22-18 AWG, #6 Stud, Avikrimp Nylon, 105°C (221°F)</b> (Reference: <a href="#">UL E32244</a> , <a href="#">CSA LR18689</a> )	
<b>19057-0009</b> (A-521-08)	<b>Ring Terminal, 22-18 AWG, #8 Stud, Avikrimp Nylon, 105°C (221°F)</b> (Reference: <a href="#">UL E32244</a> , <a href="#">CSA LR18689</a> )	
<b>19057-0011</b> (A-521-10)	<b>Ring Terminal, 22-18 AWG, #10 Stud, Avikrimp Nylon, 105°C (221°F)</b> (Reference: <a href="#">UL E32244</a> , <a href="#">CSA LR18689</a> )	

# Molex Part Number: **19413-0106 (KIT-MX11)**

Terminal Part Number	Description	Image
<b>19057-0015</b> (A-522-14)	<b>Ring Terminal, 22-18 AWG, .25" Stud, Avikrimp Nylon, 105°C (221°F)</b> (Reference: <a href="#">UL E32244</a> , <a href="#">CSA LR18689</a> )	
<b>19057-0054</b> (B-523-06)	<b>Ring Terminal, 16-14 AWG, #6 Stud, Avikrimp Nylon, 105°C (221°F)</b> (Reference: <a href="#">UL E32244</a> , <a href="#">CSA LR18689</a> )	
<b>19057-0090</b> (B-537-08)	<b>Ring Terminal, 16-14 AWG, #8 Stud, Avikrimp Nylon, 105°C (221°F)</b> (Reference: <a href="#">UL E32244</a> , <a href="#">CSA LR18689</a> )	

# Molex Part Number: **19413-0106 (KIT-MX11)**

Terminal Part Number	Description	Image
<b>19057-0093</b> (B-537-10)	<b>Ring Terminal, 16-14 AWG, #10 Stud, Avikrimp Nylon, 105°C (221°F)</b> (Reference: <a href="#">UL E32244</a> , <a href="#">CSA LR18689</a> )	
<b>19057-0060</b> (B-525-14)	<b>Ring Terminal, 16-14 AWG, .25" Stud, Avikrimp Nylon, 105°C (221°F)</b> (Reference: <a href="#">UL E32244</a> , <a href="#">CSA LR18689</a> )	
<b>19073-0110</b> (C-528-08)	<b>Ring Terminal, 12-10 AWG, #8 Stud, Avikrimp Nylon, 105°C (221°F)</b> (Reference: <a href="#">UL E32244</a> , <a href="#">CSA LR18689</a> )	

# Molex Part Number: **19413-0106 (KIT-MX11)**

Terminal Part Number	Description	Image
<b>19073-0113</b> (C-528-10)	<b>Ring Terminal, 12-10 AWG, #10 Stud, Avikrimp Nylon, 105°C (221°F)</b> (Reference: <a href="#">UL E32244</a> , <a href="#">CSA LR18689</a> )	
<b>19073-0119</b> (C-530-14)	<b>Ring Terminal, 12-10 AWG, .25" Stud, Avikrimp Nylon, 105°C (221°F)</b> (Reference: <a href="#">UL E32244</a> , <a href="#">CSA LR18689</a> )	
<b>19073-0139</b> (C-540-38)	<b>Ring Terminal, 12-10 AWG, .375" Stud, Avikrimp Nylon, 105°C (221°F)</b> (Reference: <a href="#">UL E32244</a> , <a href="#">CSA LR18689</a> )	