


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 19
 © COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

		REVISIONS			LOC	DIST
P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
✓	✓	0		RELEASED	m.s. 7-85	
✓	✓	A		REV PER DF-4316	ATG 8-91	AMM
		B		REV 0600-5691-96	TT 9-97	AMM




533637

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.010 ANGLES		CONTRACT NO DR <i>M. Smith</i> 7-18-85 CHK <i>E. A. McDougle</i> 7-25-85 APPD <i>E. A. McDougle</i> 7-25-85 APPD <i>B. Hoff</i> 7/25/85		PART NO	
MATERIAL HOUSING: ① CONTACT: ②		FINISH CONTACT: ③		AMP AMP INCORPORATED Harrisburg, Pa. 17105	
				NAME PIN HEADER ASSEMBLY, RIGHT ANGLE, 1001 SERIES, 6 COAX POSITIONS.	
		SIZE C		FSCM NO 00779	
				DRAWING NO 533637	
		SCALE 4:1		SHEET 1 OF 2	

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19
 © COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

P F ZONE LTR		DESCRIPTION	DATE	APPROVED
		SEE SHEET 1 OF 2	7-85	



1. GLASS FILLED POLYESTER. COLOR: BLUE.
2. BRASS
3. .000050 NICKEL UNDERPLATE ALL OVER. .000050 GOLD IN THIS AREA, .000100 TIN-LEAD ON SOLDER POSTS.
4. AMP PART NO. AND DATE CODE INK STAMPED WHITE THIS APPROX. AREA.
5. COAX POSITIONS (A, B, C, D, E & F) INK STAMPED WHITE THIS AREA.
6. WILL ACCEPT MICROMINIATURE COAX CONTACT, AMP P/N 227602-1 & 227604-1, INSERT CONTACT P/N 227602-1 FROM THIS SIDE BEFORE MTG. TO P.C. BD. OR ACCEPTS COAX CABLE CONTACT.
7. CONTACT POS. STAMPED ON THIS SIDE, AND NUMBERS INDICATING EVERY FIFTH CAVITY STAMPED ON SIDE. NUMBERS INDICATING END CAVITIES STAMPED ON MATING FACE AND LINES INDICATING EVERY FIFTH CAVITY STAMPED ON MATING FACE.

	E	D	C	B	A	No. of COAX POS.	No. of BOX POS.	PART NO
OBS	5.500	55	7.175	7.564	7.855	6	112	1-533637-0
OBS	5.000	50	6.675	7.064	7.355	↑	102	↑ -9
OBS	4.500	45	6.175	6.564	6.855	↑	92	↑ -8
OBS	4.000	40	5.675	6.064	6.355	↑	82	↑ -7
OBS	3.500	35	5.175	5.564	5.855	↑	72	↑ -6
	3.000	30	4.675	5.064	5.355	↑	62	↑ -5
OBS	2.500	25	4.175	4.564	4.855	↑	52	↑ -4
OBS	2.000	20	3.675	4.064	4.355	↑	42	↑ -3
OBS	1.500	15	3.175	3.564	3.855	↓	32	↓ -2
OBS	1.000	10	2.675	3.064	3.355	↓	22	↓ -1

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.010 ANGLES ±	CONTRACT NO	AMP AMP INCORPORATED Harrisburg, Pa. 17105	
	MATERIAL	DR <i>M. Smith</i> 7-19-85 CHK <i>E. A. McDougle</i> 7-25-85 APPD <i>E. A. McDougle</i> 7-25-85 APPD <i>E. A. McDougle</i> 7/25/85	NAME PIN HEADER ASSEMBLY, RIGHT ANGLE, 1001 SERIES, 6 COAX POSITIONS.
FINISH	OTHER APPD	SIZE C	FSCM NO 00779
		SCALE 4:1	DRAWING NO 533637
		SHEET 2	