


TERMINALS


10-133-X-01



RECOMMENDED MOUNTING HOLE
.033 DIA (#66 DRILL)

NO.	L	T	MATERIAL
10-133-1A	.037	1/64	Brass
10-133-1	.053	1/32	FINISH
10-133-2	.084	1/16	Silver
10-133-3	.115	3/32	


10-121-X-05



RECOMMENDED MOUNTING HOLE
.052 DIA (#55 DRILL)

NO.	L	T	MATERIAL
10-121-1	.051	1/32	Brass
10-121-2	.082	1/16	FINISH
			Electro-Solder


10-107-X-01



RECOMMENDED MOUNTING HOLE
.067 DIA (#51 DRILL)

NO.	L	T	D	MATERIAL
10-107-11	.025	1/64	.020	Brass
10-107-1	.045	1/32	.040	FINISH
10-107-2	.094	1/16	.089	Silver
10-107-3	.125	3/32	.089	


10-115-X-044



RECOMMENDED MOUNTING HOLE
.037 DIA (#63 DRILL)

NO.	L	T	MATERIAL
10-115-1	.051	1/32	Brass
10-115-2	.084	1/16	FINISH
10-115-2B	.096	1/16	Vinillate


10-120-X-01



RECOMMENDED MOUNTING HOLE
.052 DIA (#55 DRILL)

NO.	L	T	MATERIAL
10-120-2	.094	1/16	Brass
			FINISH
			Silver


12-117-X-01



MATERIAL
Brass
FINISH
Silver

NO.	L	T	NO.	L	T
12-117-11	.037	1/64	12-117-3	.115	3/32
12-117-1	.053	1/32	12-117-4	.147	1/8
12-117-2	.084	1/16			


10-136-X-05



RECOMMENDED MOUNTING HOLE
.041 DIA (#60 DRILL)

NO.	L	T	MATERIAL
10-136-1	.055	1/32	Brass
10-136-2	.084	1/16	FINISH
			Electro-Solder


10-127-1-05



RECOMMENDED MOUNTING HOLE
.055 DIA (#54 DRILL)

NO.	L	T	MATERIAL
10-127-1	.130	.062 TO .094	Brass
			FINISH
			Silver
			Electro-Solder


10-138-X-XX



RECOMMENDED MOUNTING HOLE
.067 DIA (#51 DRILL)


NO.	L	T	D	MATERIAL
10-138-1	.045	1/32	.040	Brass
10-138-2	.094	1/16	.062	FINISHES
10-138-3	.125	3/32	.062	(01) Silver
10-138-4	.156	1/8	.062	(04) Electro-Tin

12-114-X-01



NO.	L	T	MATERIAL
12-114-11	.037	1/64	Brass
12-114-1	.053	1/32	FINISH
12-114-2	.084	1/16	Silver
12-114-3	.115	3/32	
12-114-4	.147	1/8	


10-129-2-04



RECOMMENDED MOUNTING HOLE
.055 DIA (#54 DRILL)

NO.	L	T	MATERIAL
10-129-2	.100	.062	Brass
			FINISH
			Electro-Tin


10-101-X-XX



RECOMMENDED MOUNTING HOLE
.076 DIA (#48 DRILL)

NO.	L	T	MATERIAL
10-101-1	.051	1/32	Brass
10-101-2	.082	1/16	
10-101-3	.113	3/32	FINISHES
10-101-4	.145	1/8	(01) Silver
10-101-6	.207	3/16	(05) Electro-Solder
10-101-8	.270	1/4	


10-104-X-XX



RECOMMENDED MOUNTING HOLE
.052 DIA (#55 DRILL)

NO.	L	T	MATERIAL
10-104-11	.035	1/64	Brass
10-104-1	.051	1/32	FINISHES
10-104-2	.082	1/16	(01) Silver
10-104-3	.113	3/32	(03) Gold/Copper
10-104-4	.145	1/8	


13-108-X-01



RECOMMENDED MOUNTING HOLE
.067 DIA (#51 DRILL)

NO.	L	T	MATERIAL
13-108-11	.037	1/64	Brass
13-108-1	.054	1/32	FINISH
13-108-2	.084	1/16	Silver
13-108-3	.115	3/32	
13-108-4	.147	1/8	


12-105-X-01



NO.	L	T	MATERIAL
12-105-11	.037	1/64	Brass
12-105-1	.053	1/32	FINISH
12-105-2	.084	1/16	Silver
12-105-3	.115	3/32	
12-105-4	.147	1/8	

TERMINALS

10-134-X-05




RECOMMENDED MOUNTING HOLE
.081 DIA (#46 DRILL)

NO.	L	T	MATERIAL
10-134-1	.062	1/32	Brass
10-134-2	.094	1/16	Brass
10-134-3	.125	3/32	Brass
10-134-4	.156	1/8	Brass

FINISH
Electro-Solder

11-111-X-01




RECOMMENDED MOUNTING HOLE
.094 DIA (3/32 DRILL)

NO.	L	T	MATERIAL
11-111-1	.075	1/32	Brass
11-111-2	.105	1/16	Brass
11-111-3	.135	3/32	Brass
11-111-4	.165	1/8	Brass
11-111-5	.195	5/32	Brass

FINISH
Silver

10-135-X-04




RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)

NO.	L	T	MATERIAL
10-135-1	.078	1/32	Brass
10-135-2	.109	1/16	Brass
10-135-3	.140	3/32	Brass
10-135-4	.171	1/8	Brass

FINISH
Electro-Tin


12-112-X-01



MATERIAL
Brass

NO.	L	T	FINISH
12-112-1	.075	1/32	Silver
12-112-2	.105	1/16	Silver
12-112-3	.135	3/32	Silver
12-112-4	.165	1/8	Silver

13-106-X-01




RECOMMENDED MOUNTING HOLE
.094 DIA (3/32 DRILL)

NO.	L	T	MATERIAL
13-106-1	.075	1/32	Brass
13-106-2	.105	1/16	Brass
13-106-3	.135	3/32	Brass
13-106-4	.165	1/8	Brass

FINISH
Silver


12-229-X-01



MATERIAL
Brass

NO.	L	T	FINISH
12-229-1	.053	1/32	Silver
12-229-2	.084	1/16	Silver
12-229-3	.115	3/32	Silver

10-102-X-XX




*FOR-1 IS 068
RECOMMENDED MOUNTING HOLE
.082 DIA (#45 DRILL)

NO.	L	T	MATERIAL
10-102-1	.078	1/32	Brass
10-102-2	.109	1/16	Brass
10-102-3	.141	3/32	Brass
10-102-4	.172	1/8	Brass

FINISHES
(01) Silver
(03) Gold/Copper

10-109-X-01




RECOMMENDED MOUNTING HOLE
.094 DIA (#42 DRILL)

NO.	L	T	MATERIAL
10-109-1	.062	1/32	Brass
10-109-2	.094	1/16	Brass
10-109-3	.125	3/32	Brass
10-109-4	.156	1/8	Brass
10-109-6	.219	3/16	Brass

FINISH
Silver


12-227-X-01



MATERIAL
Brass

NO.	L	T	FINISH
12-227-1	.037	1/64	Silver
12-227-2	.053	1/32	Silver
12-227-3	.115	3/32	Silver
12-227-4	.147	1/8	Silver

11-119-X-01




RECOMMENDED MOUNTING HOLE
.082 DIA (#45 DRILL)

NO.	L	T	MATERIAL
11-119-1	.075	1/32	Brass
11-119-2	.105	1/16	Brass
11-119-3	.135	3/32	Brass
11-119-4	.165	1/8	Brass

FINISH
Silver

10-137-X-01




RECOMMENDED MOUNTING HOLE
.094 DIA (3/32 DRILL)

NO.	L	T	MATERIAL
10-137-1	.078	1/32	Brass
10-137-2	.109	1/16	Brass
10-137-3	.141	3/32	Brass
10-137-4	.172	1/8	Brass
10-137-099	.099	1/16	Brass

FINISH
Silver

10-232-X-05




RECOMMENDED MOUNTING HOLE
.052 DIA (#55 DRILL)

NO.	L	T	MATERIAL
10-232-1	.047	1/32	Brass
10-232-2	.080	1/16	Brass

FINISH
Electro-Solder

10-130-X-05




RECOMMENDED MOUNTING HOLE
.094 DIA (3/32 DRILL)

NO.	L	T	MATERIAL
10-130-1	.062	1/32	Brass
10-130-2	.094	1/16	Brass
10-130-4	.141	1/8	Brass

FINISH
Electro-Solder

10-103-X-XX




RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)

NO.	L	T	MATERIAL
10-103-1	.078	1/32	Brass
10-103-2	.109	1/16	Brass
10-103-3	.141	3/32	Brass
10-103-4	.172	1/8	Brass
10-103-6	.234	3/16	Brass
10-103-8	.297	1/4	Brass

FINISHES
(01) Silver
(03) Gold/Copper

10-214-X-XX



RECOMMENDED MOUNTING HOLE
.067 DIA (#51 DRILL)

NO.	L	T	MATERIAL
10-214-1	.037	1/64	Brass
10-214-2	.053	1/32	Brass
10-214-3	.084	1/16	Brass
10-214-4	.115	3/32	Brass
10-214-4	.147	1/8	Brass

FINISHES
(01) Silver
(03) Gold/Copper
(05) Electro-Solder


FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY

CONCORD
THE COMPONENT PEOPLE

30 GREAT JONES STREET
NEW YORK, N.Y. 10012-1115
(212) 777-6571 • 1-800-847-4162
FAX (212) 995-0161


TERMINALS

11-215-X-01



NO	L	T	RECOMMENDED MOUNTING HOLE	MATERIAL	FINISH
11-215-1	.037	1/64	.064 DIA (#52 DRILL)	Brass	Silver
11-215-2	.053	1/32			
11-215-3	.084	1/16			
11-215-4	.115	3/32			
11-215-5	.147	1/8			
11-215-6	.178	5/32			
11-215-7	.209	3/16			


10-201-X-XX



RECOMMENDED MOUNTING HOLE
.076 DIA (#48 DRILL)


NO	L	T	RECOMMENDED MOUNTING HOLE	MATERIAL	FINISH
10-201-1	.051	1/32		Brass	Silver
10-201-2	.082	1/16			
10-201-3	.113	3/32			
10-201-4	.145	1/8			
10-201-5	.176	5/32			
10-201-6	.207	3/16			
10-201-7	.238	1/4			

10-228-X-01




NO	L	T	RECOMMENDED MOUNTING HOLE	MATERIAL	FINISH
10-228-1	.062	1/32	.094 DIA (#42 DRILL) *FOR -1 IS .047	Aluminum	Silver
10-228-2	.094	1/16			
10-228-3	.125	3/32			
10-228-4	.156	1/8			
10-228-5	.187	5/32			
10-228-6	.218	3/16			
10-228-7	.249	1/4			

11-225-X-01




NO	L	T	RECOMMENDED MOUNTING HOLE	MATERIAL	FINISH
11-225-1	.037	1/64	.067 DIA (#51 DRILL)	Brass	Silver
11-225-2	.053	1/32			
11-225-3	.084	1/16			
11-225-4	.115	3/32			
11-225-5	.147	1/8			
11-225-6	.178	5/32			
11-225-7	.209	3/16			

12-206-X-01




NO	L	T	RECOMMENDED MOUNTING HOLE	MATERIAL	FINISH
12-206-1	.053	1/32		Brass	Silver
12-206-2	.084	1/16			
12-206-3	.115	3/32			
12-206-4	.147	1/8			

10-216-X-XX




NO	L	T	RECOMMENDED MOUNTING HOLE	MATERIAL	FINISHES
10-216-1	.075	1/32	.094 DIA (#42 DRILL)	Brass	(01) Silver
10-216-2	.105	1/16			(05) Electro-Solder
10-216-3	.135	3/32			
10-216-4	.165	1/8			
10-216-5	.195	5/32			
10-216-6	.225	3/16			
10-216-7	.255	1/4			

13-220-X-01




NO	L	T	RECOMMENDED MOUNTING HOLE	MATERIAL	FINISH
13-220-1	.037	1/64	.064 DIA (#52 DRILL)	Brass	Silver
13-220-2	.053	1/32			
13-220-3	.084	1/16			
13-220-4	.115	3/32			
13-220-5	.147	1/8			

11-221-X-01




NO	L	T	RECOMMENDED MOUNTING HOLE	MATERIAL	FINISH
11-221-1	.053	1/32	.078 DIA (#48 DRILL)	Brass	Silver
11-221-2	.084	1/16			
11-221-3	.115	3/32			
11-221-4	.147	1/8			

13-218-X-01




NO	L	T	RECOMMENDED MOUNTING HOLE	MATERIAL	FINISH
13-218-1	.075	1/32	.094 DIA (3/32 DRILL)	Brass	Silver
13-218-2	.105	1/16			
13-218-3	.135	3/32			
13-218-4	.165	1/8			

10-233-A-04




NO	L	T	RECOMMENDED MOUNTING HOLE	MATERIAL	FINISH
10-233-A	.125	3/32	.073 DIA (#49 DRILL)	Brass	Electro-Tin

10-209-X-XX




NO	L	T	RECOMMENDED MOUNTING HOLE	MATERIAL	FINISHES
10-209-1	.078	1/32	.094 DIA (3/32 DRILL)	Brass	(01) Silver
10-209-2	.109	1/16			(03) Gold/Copper
10-209-3	.141	3/32			
10-209-4	.172	1/8			
10-209-5	.204	5/32			
10-209-6	.235	3/16			
10-209-7	.266	1/4			

10-243-2-05




NO	L	T	RECOMMENDED MOUNTING HOLE	MATERIAL	FINISH
10-243-2	.062 TO .094			Brass	Electro-Solder

10-248-2-05




NO	L	T	RECOMMENDED MOUNTING HOLE	MATERIAL	FINISH
10-248-2	.105	1/16	.073 DIA (#49 DRILL)	Brass	Electro-Solder

10-259-X-01



NO	L	T	RECOMMENDED MOUNTING HOLE	MATERIAL	FINISH
10-259-1	.062	1/32	.094 DIA (3/32 DRILL)	Brass	Silver
10-259-2	.094	1/16			
10-259-3	.125	3/32			
10-259-4	.156	1/8			
10-259-5	.187	5/32			
10-259-6	.218	3/16			
10-259-7	.249	1/4			

13-207-X-01




NO	L	T	RECOMMENDED MOUNTING HOLE	MATERIAL	FINISH
13-207-1	.075	1/32	.094 DIA (3/32 DRILL)	Brass	Silver
13-207-2	.105	1/16			
13-207-3	.135	3/32			
13-207-4	.165	1/8			

FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY


TERMINALS

10-203-X-01




NO.	L	T	RECOMMENDED MOUNTING HOLE	MATERIAL
10-203-1	.078	1/32	.094 DIA (#42 DRILL)	Brass
10-203-2	.109	1/16		Brass
10-203-3	.141	3/32		Brass
10-203-4	.172	1/8		Brass
10-203-6	.234	3/16		Brass
10-203-8	.297	1/4		Brass

10-247-X-01



NO.	L	T	RECOMMENDED MOUNTING HOLE	MATERIAL
10-247-1	.078	1/32	.116 DIA (#32 DRILL)	Brass
10-247-2	.109	1/16		Brass
10-247-3	.141	3/32		Brass
10-247-4	.172	1/8		Brass
10-247-6	.234	3/16		Brass
10-247-8	.297	1/4		Brass


10-238-X-01



RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)

NO.	L	T	MATERIAL
10-238-1	.078	1/32	Brass
10-238-2	.109	1/16	Brass
10-238-3	.141	3/32	Brass
10-238-4	.172	1/8	Brass


10-231-X-01



RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)

NO.	L	T	MATERIAL
10-231-2	.105	1/16	Brass
10-231-3	.135	3/32	Brass
10-231-4	.165	1/8	Brass


10-204-X-XX



RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)


NO.	L	T	MATERIAL	FINISHES
10-204-1	.078	1/32	Brass	(01) Silver
10-204-2	.109	1/16	Brass	(03) Gold/Copper
10-204-3	.141	3/32	Brass	(05) Electro-Solder
10-204-4	.172	1/8	Brass	
10-204-6	.234	3/16	Brass	
10-204-8	.297	1/4	Brass	

12-210-X-01



NO.	L	T	MATERIAL
12-210-2	.105	1/16	Brass
12-210-3	.135	3/32	Brass
12-210-4	.165	1/8	Brass


10-230-X-01



RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)

NO.	L	T	MATERIAL
10-230-2	.105	1/16	Brass
10-230-3	.135	3/32	Brass
10-230-4	.165	1/8	Brass


19-246-X-09



RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)

NO.	L	T	D	MATERIAL	FINISH
19-246-2	.109	1/16	.078	Leaded	Hot Solder Dip
19-246-3	.141	3/32	.094	Commercial	
19-246-4	.172	1/8	.109	Brenze	
19-246-6	.234	3/16	.135		


11-226-X-01



RECOMMENDED MOUNTING HOLE
.206 DIA (#5 DRILL)


NO.	L	T	MATERIAL
11-226-1	.075	1/32	Brass
11-226-2	.105	1/16	Brass
11-226-3	.135	3/32	Brass
11-226-4	.165	1/8	Brass

12-212-X-01



NO.	L	T	MATERIAL
12-212-1	.075	1/32	Brass
12-212-2	.105	1/16	Brass
12-212-3	.135	3/32	Brass
12-212-4	.165	1/8	Brass


13-205-X-01



RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)

NO.	L	T	MATERIAL
13-205-1	.075	1/32	Brass
13-205-2	.105	1/16	Brass
13-205-3	.135	3/32	Brass
13-205-4	.165	1/8	Brass
13-205-5	.195	5/32	Brass
13-205-6	.230	3/16	Brass


10-211-X-XX



RECOMMENDED MOUNTING HOLE
.266 DIA (17/64 DRILL)

NO.	L	T	MATERIAL
10-211-2	.109	1/16	Brass
10-211-3	.141	3/32	Brass
10-211-4	.172	1/8	Brass
10-211-6	.234	3/16	Brass
10-211-8	.297	1/4	Brass


13-217-X-01



RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)


NO.	L	T	MATERIAL
13-217-1	.075	1/32	Brass
13-217-2	.105	1/16	Brass
13-217-3	.135	3/32	Brass
13-217-4	.165	1/8	Brass
13-217-5	.195	5/32	Brass
13-217-6	.230	3/16	Brass

12-240-X-01



NO.	L	T	MATERIAL
12-240-1	.075	1/32	Brass
12-240-2	.105	1/16	Brass
12-240-3	.135	3/32	Brass
12-240-4	.165	1/8	Brass

10-222-1-01




RECOMMENDED MOUNTING HOLE
.128 ± .002 DIA
PRESS TO .085 MIN DEPTH

NO.	L	T	MATERIAL
10-222-1	.075	1/32	Brass
10-222-2	.105	1/16	Brass
10-222-3	.135	3/32	Brass
10-222-4	.165	1/8	Brass

TERMINALS


10-223-1-01



RECOMMENDED MOUNTING HOLE
.161 ± .002 DIA
PRESS TO .085 MIN. DEPTH

MATERIAL
Brass
FINISH
Silver

10-302-X-05




RECOMMENDED MOUNTING HOLE
.067 DIA (#51 DRILL)

NO	L	T
10-302-2	084	1/16
10-302-3	115	3/32
10-302-4	147	1/8

MATERIAL
Brass
FINISH
Electro
Solder Plate

10-335-X-04




RECOMMENDED MOUNTING HOLE
.081 DIA (#46 DRILL)

NO	L	T
10-335-2	093	1/16
10-335-3	125	3/32

MATERIAL
Brass
FINISH
Tin Plate


10-224-1-01



RECOMMENDED MOUNTING HOLE
.195 ± .002 DIA
PRESS TO .085 MIN. DEPTH

MATERIAL
Brass
FINISH
Silver

11-323-X-01




RECOMMENDED MOUNTING HOLE
.076 DIA (#48 DRILL)

NO	L	T
11-323-11	037	1/64
11-323-1	053	1/32
11-323-2	084	1/16
11-323-3	115	3/32
11-323-4	147	1/8
11-323-5	178	5/32
11-323-6	209	3/16

MATERIAL
Brass
FINISH
Silver

12-312-X-01




RECOMMENDED MOUNTING HOLE

NO	L	T
12-312-1	.075	1/32
12-312-2	.105	1/16
12-312-3	.135	3/32
12-312-4	.165	1/8

MATERIAL
Brass
FINISH
Silver

10-308-X-01




RECOMMENDED MOUNTING HOLE
.067 DIA (#51 DRILL)

NO	L	T	D
10-308-11	.025	1/64	.020
10-308-1	.045	1/32	.040
10-308-2	.094	1/16	.089
10-308-3	.125	3/32	.089

MATERIAL
Brass
FINISH
Silver

10-301-X-01




RECOMMENDED MOUNTING HOLE
.076 DIA (#48 DRILL)

NO	L	T
10-301-1	062	1/32
10-301-2	094	1/16
10-301-3	125	3/32
10-301-4	156	1/8

MATERIAL
Brass
FINISH
Silver

13-315-X-01




RECOMMENDED MOUNTING HOLE
.082 DIA (#45 DRILL)

NO	L	T
13-315-1	.075	1/32
13-315-2	.105	1/16
13-315-3	.135	3/32
13-315-4	.165	1/8

MATERIAL
Brass
FINISH
Silver

10-333-2-XX




RECOMMENDED MOUNTING HOLE
.084 DIA (#52 DRILL)

NO	L	T
10-333-2	.094	1/16

MATERIAL
Brass
FINISH
Silver/
Tin Plate

13-341-X-01




RECOMMENDED MOUNTING HOLE
.076 DIA (#48 DRILL)

NO	L	T
13-341-11	037	1/64
13-341-1	054	1/32
13-341-2	084	1/16
13-341-3	115	3/32
13-341-4	147	1/8

MATERIAL
Brass
FINISH
Silver

10-330-X-04




RECOMMENDED MOUNTING HOLE
.086 DIA (#44 DRILL)

NO	L	T
10-330-2A	094	3/64
10-330-2	109	1/16
10-330-3	141	3/32

MATERIAL
Brass
FINISH
Electro-Tin

10-360-2-05




RECOMMENDED MOUNTING HOLE
.064 DIA (#52 DRILL)

NO	L	T
10-360-2	105	1/16

MATERIAL
Brass
FINISH
Electro
Solder Plate

14-346-X-05




RECOMMENDED MOUNTING HOLE
.082 DIA (#45 DRILL)

NO	L	T
14-346-2	109	1/16
14-346-3	135	3/32
14-346-4	172	1/8

MATERIAL
Leaded
Commercial Bronze
FINISH
Electro
Solder Plate

10-331-X-04



RECOMMENDED MOUNTING HOLE
.086 DIA (#44 DRILL)

NO	L	T
10-331-2	109	1/16
10-331-3	141	3/32
10-331-4	172	1/8


MATERIAL
Brass
FINISH
Electro-Tin

FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY

30 GREAT JONES STREET
NEW YORK, N.Y. 10012-1115
(212) 777-6571 • TWX 710-581-4930
FAX (212) 995-0161


TERMINALS

11-320-X-01




NO	L	T	MATERIAL
11-320-1	.075	1/32	Brass
11-320-2	.105	1/16	
11-320-3	.135	3/32	FINISH
11-320-4	.165	1/8	Silver

11-307-X-01




NO	L	T	MATERIAL
11-307-1	.075	1/32	Brass
11-307-2	.105	1/16	
11-307-3	.135	3/32	FINISH
11-307-4	.165	1/8	Silver

12-317-X-01




NO	L	T	MATERIAL
12-317-1	.075	1/32	Brass
12-317-2	.105	1/16	
12-317-3	.135	3/32	FINISH
12-317-4	.165	1/8	Silver

12-303-X-01




NO	L	T	MATERIAL
12-303-1	.075	1/32	Brass
12-303-2	.105	1/16	
12-303-3	.135	3/32	FINISH
12-303-4	.165	1/8	Silver

10-305-X-01




NO	L	T	MATERIAL
10-305-1	.078	1/32	Brass
10-305-2	.109	1/16	
10-305-3	.141	3/32	FINISH
10-305-4	.172	1/8	Silver

11-309-X-01




NO	L	T	MATERIAL
11-309-1	.075	1/32	Brass
11-309-2	.105	1/16	
11-309-3	.135	3/32	FINISH
11-309-4	.165	1/8	
11-309-5	.195	5/32	FINISH
11-309-6	.230	3/16	Silver

10-321-X-01




NO	L	T	MATERIAL
10-321-1	.062	1/32	Brass
10-321-2	.094	1/16	
10-321-3	.125	3/32	FINISH
10-321-4	.156	1/8	Silver

12-306-X-01




NO	L	T	MATERIAL
12-306-1	.075	1/32	Brass
12-306-2	.105	1/16	
12-306-3	.135	3/32	FINISH
12-306-4	.165	1/8	Silver

10-349-X-05




NO	L	T	MATERIAL
10-349-2	.109	1/16	Brass
10-349-3	.141	3/32	FINISH
10-349-4	.172	1/8	Electro Solder Plate

11-313-X-01




NO	L	T	MATERIAL
11-313-1	.075	1/32	Brass
11-313-2	.105	1/16	
11-313-3	.135	3/32	FINISH
11-313-4	.165	1/8	Silver

13-310-X-01




NO	L	T	MATERIAL
13-310-1	.075	1/32	Brass
13-310-2	.105	1/16	
13-310-3	.135	3/32	FINISH
13-310-4	.165	1/8	
13-310-5	.195	5/32	FINISH
13-310-6	.230	3/16	Silver

11-318-X-01




NO	L	T	MATERIAL
11-318-1	.075	1/32	Brass
11-318-2	.105	1/16	
11-318-3	.135	3/32	FINISH
11-318-4	.165	1/8	Silver

14-345-X-05




NO	L	T	MATERIAL
14-345-2	.109	1/16	Leaded Commercial Bronze
14-345-3	.135	3/32	
14-345-4	.172	1/8	FINISH
14-345-5	.195	5/32	Electro Solder Plate

10-311-X-01



NO	L	T	MATERIAL
10-311-1	.078	1/32	Brass
10-311-2	.109	1/16	
10-311-3	.141	3/32	FINISH
10-311-4	.172	1/8	
10-311-6	.234	3/16	Silver
10-311-8	.297	1/4	

13-316-X-01




NO	L	T	MATERIAL
13-316-1	.075	1/32	Brass
13-316-2	.105	1/16	
13-316-3	.135	3/32	FINISH
13-316-4	.165	1/8	Silver

FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY

30 GREAT JONES STREET
NEW YORK, N.Y. 10012-1115
(212) 777-6571 • TWX 710-581-4930
FAX (212) 995-0161

TERMINALS


14-347-X-05



RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)

NO.	L	T	MATERIAL	FINISH
14-347-2	.109	1/16	Leaded Commercial Bronze	Electro Solder Plate
14-347-3	.135	3/32		
14-347-4	.172	1/8		
14-347-5	.195	5/32		


10-304-X-01



RECOMMENDED MOUNTING HOLE
.1405 DIA (#28 DRILL)

NO.	L	T	MATERIAL	FINISH
10-304-2	.109	1/16	Brass	
10-304-3	.141	3/32		
10-304-4	.172	1/8		
10-304-6	.234	3/16		


10-431-X-05



RECOMMENDED MOUNTING HOLE
.036 DIA (#64 DRILL)

NO.	L	T	MATERIAL	FINISH
10-431-11	.030	1/64	Brass	
10-431-1	.045	1/32		
10-431-2	.077	1/16		
10-431-3	.108	3/32		
10-431-4	.139	1/8		


10-336-X-04



RECOMMENDED MOUNTING HOLE
.126 DIA (1/8 DRILL)


NO.	L	T	MATERIAL	FINISH
10-336-1	.109	1/16	Brass	
10-336-2	.125	3/32		
10-336-3	.156	1/8		

12-325-X-01




NO.	L	T	MATERIAL	FINISH
12-325-2	.105	1/16	Brass	
12-325-3	.135	3/32		
12-325-4	.165	1/8		

12-444-X-01



NO.	L	T	MATERIAL	FINISH
12-444-11	.037	1/64	Brass	
12-444-1	.053	1/32		
12-444-2	.084	1/16		
12-444-3	.115	3/32		
12-444-4	.147	1/8		


10-329-X-04



RECOMMENDED MOUNTING HOLE
.125 DIA (1/8 DRILL)


NO.	L	T	MATERIAL	FINISH
10-329-2	.109	1/16	Brass	
10-329-3	.141	3/32		
10-329-4	.172	1/8		
10-329-5	.203	5/32		
10-329-6	.234	3/16		

14-351-X-05




NO.	L	A	T	MATERIAL	FINISH
14-351-2	.109	.054	1/16	Leaded Commercial Bronze	
14-351-3	.135	.084	3/32		
14-351-4	.172	.113	1/8		
14-351-5	.195	.145	5/32		
14-351-6	.230	.171	3/16		

12-461-X-01



NO.	L	T	MATERIAL	FINISH
12-461-11	.037	1/64	Brass	
12-461-1	.053	1/32		
12-461-2	.084	1/16		
12-461-3	.115	3/32		
12-461-4	.147	1/8		


10-337-X-04



RECOMMENDED MOUNTING HOLE
.125 DIA (1/8 DRILL)


NO.	L	T	MATERIAL	FINISH
10-337-2	.109	1/16	Brass	
10-337-3	.141	3/32		
10-337-4	.172	1/8		

14-350-X-05



NO.	L	A	T	MATERIAL	FINISH
14-350-2	.109	.054	1/16	Leaded Commercial Bronze	
14-350-3	.135	.084	3/32		
14-350-4	.172	.113	1/8		
14-350-5	.195	.145	5/32		
14-350-6	.230	.171	3/16		


10-453-X-01



RECOMMENDED MOUNTING HOLE
.062 DIA (#55 DRILL)

NO.	L	T	MATERIAL	FINISH
10-453-11	.035	1/64	Brass	
10-453-1	.051	1/32		
10-453-2	.082	1/16		
10-453-3	.113	3/32		
10-453-4	.145	1/8		
10-453-5	.207	3/16		
10-453-6	.270	1/4		


10-332-4A-04



RECOMMENDED MOUNTING HOLE
.125 DIA (1/8 DRILL)


NO.	L	T	MATERIAL	FINISH
10-332-4A	.136	7/64	Brass	Tin Plate

12-464-X-01



NO.	L	T	MATERIAL	FINISH
12-464-11	.037	1/64	Brass	
12-464-1	.053	1/32		
12-464-2	.084	1/16		
12-464-3	.115	3/32		
12-464-4	.147	1/8		

10-413-X-01


















NO.	L	T	MATERIAL	FINISH
10-413-11	.035	1/64	Brass	
10-413-1	.051	1/32		
10-413-2	.082	1/16		
10-413-3	.113	3/32		
10-413-4	.145	1/8		
10-413-5	.207	3/16		
10-413-6	.270	1/4		

FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY

30 GREAT JONES STREET
NEW YORK, N.Y. 10012-1115
(212) 777-6571 • TWX 710-581-4930
FAX (212) 995-0161

TAPERED SOCKETS/TERMINALS



**MOST ITEMS ARE IN STOCK
AND SHIPPED OUT
THE SAME DAY**


FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY

**30 GREAT JONES STREET
NEW YORK, N.Y. 10012-1115
(212) 777-6571 • TWX 710-581-4930
FAX (212) 995-0161**

CONCORD
THE COMPONENT PEOPLE

TERMINALS


12-462-X-01



NO.	L	T
12-462-11	.037	1/64
12-462-1	.053	1/32
12-462-2	.084	1/16
12-462-3	.115	3/32
12-462-4	.147	1/8
12-462-6	.209	3/16

MATERIAL
Brass
FINISH
Silver


12-459-X-01



NO.	L	T
12-459-11	.037	1/64
12-459-1	.053	1/32
12-459-2	.084	1/16
12-459-3	.115	3/32
12-459-4	.147	1/8
12-459-5	.178	5/32
12-459-6	.209	3/16

MATERIAL
Brass
FINISH
Silver


12-430-X-01



NO.	L	T
12-430-11	.037	1/64
12-430-1	.053	1/32
12-430-2	.084	1/16
12-430-3	.115	3/32
12-430-4	.147	1/8

MATERIAL
Brass
FINISH
Silver


10-414-X-01



NO.	L	T
10-414-11	.035	1/64
10-414-1	.051	1/32
10-414-2	.082	1/16
10-414-3	.113	3/32
10-414-4	.145	1/8
10-414-6	.207	3/16
10-414-8	.270	1/4

RECOMMENDED MOUNTING HOLE
.062 DIA. (#55 DRILL)
MATERIAL
Brass
FINISH
Silver


10-489-X-01



NO.	L	T	D
10-489-11	.025	1/64	.040
10-489-1	.045	1/32	.040
10-489-2	.094	1/16	.062
10-489-3	.125	3/32	.062
10-489-4	.156	1/8	.062

RECOMMENDED MOUNTING HOLE .087 DIA (#51 DRILL)
MATERIAL
Brass
FINISH
Silver


12-447-X-01



NO.	L	T
12-447-11	.037	1/64
12-447-1	.053	1/32
12-447-2	.084	1/16
12-447-3	.115	3/32
12-447-4	.147	1/8

MATERIAL
Brass
FINISH
Silver


10-415-X-01



NO.	L	T
10-415-11	.035	1/64
10-415-1	.051	1/32
10-415-2	.082	1/16
10-415-3	.113	3/32
10-415-4	.145	1/8
10-415-6	.207	3/16
10-415-8	.270	1/4

RECOMMENDED MOUNTING HOLE
.062 DIA (#55 DRILL)
MATERIAL
Brass
FINISH
Silver


10-477-X-01



NO.	L	T
10-477-11	.037	1/64
10-477-1	.053	1/32
10-477-2	.084	1/16
10-477-3	.115	3/32
10-477-4	.147	1/8
10-477-5	.179	5/32
10-477-6	.218	3/16

RECOMMENDED MOUNTING HOLE .064 DIA (#51 DRILL)
MATERIAL
Brass
FINISH
Silver


12-460-X-01



NO.	L	T
12-460-11	.037	1/64
12-460-1	.053	1/32
12-460-2	.084	1/16
12-460-3	.115	3/32
12-460-4	.147	1/8

MATERIAL
Brass
FINISH
Silver


10-401-X-01



NO.	L	T
10-401-11	.025	1/64
10-401-1	.045	1/32
10-401-2	.094	1/16
10-401-3	.125	3/32
10-401-4	.156	1/8
10-401-6	.219	3/16
10-401-8	.281	1/4

RECOMMENDED MOUNTING HOLE
.067 DIA (#51 DRILL)
MATERIAL
Brass
FINISH
Silver


12-449-X-01



NO.	L	T
12-449-11	.037	1/64
12-449-1	.053	1/32
12-449-2	.084	1/16
12-449-3	.115	3/32
12-449-4	.147	1/8

MATERIAL
Brass
FINISH
Silver


12-448-X-01



NO.	L	T
12-448-11	.037	1/64
12-448-1	.053	1/32
12-448-2	.084	1/16
12-448-3	.115	3/32
12-448-4	.147	1/8

MATERIAL
Brass
FINISH
Silver


12-471-X-01



NO.	L	T	NO.	L	T
12-471-11	.037	1/64	12-471-4	.147	1/8
12-471-1	.053	1/32	12-471-5	.178	5/32
12-471-2	.084	1/16	12-471-6	.209	3/16
12-471-3	.115	3/32			

MATERIAL
Brass
FINISH
Silver


12-416-X-01



NO.	L	T
12-416-11	.037	1/64
12-416-1	.053	1/32
12-416-2	.084	1/16
12-416-3	.115	3/32
12-416-4	.147	1/8

MATERIAL
Brass
FINISH
Silver

10-457-X-XX



NO.	L	T
10-457-11	.025	1/64
10-457-1	.045	1/32
10-457-2	.094	1/16
10-457-3	.125	3/32
10-457-4	.156	1/8
10-457-6	.219	3/16
10-457-8	.281	1/4


RECOMMENDED MOUNTING HOLE
.076 DIA (#48 DRILL)
MATERIAL
Brass
FINISHES
(01) Silver
(06) Electro-Solder

FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY

30 GREAT JONES STREET
NEW YORK, N.Y. 10012-1115
(212) 777-6571 • 1-800-847-4162
FAX (212) 995-0161

TERMINALS


10-405-X-01



RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)

NO	L	T	MATERIAL
10-405-1	.078	1/32	Brass
10-405-2	.109	1/16	
10-405-3	.141	3/32	
10-405-4	.172	1/8	
10-405-6	.234	3/16	FINISH Silver
10-405-8	.297	1/4	


10-482-X-01



RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)

NO	L	T	MATERIAL
10-482-1	.078	1/32	Brass
10-482-2	.109	1/16	
10-482-3	.141	3/32	FINISH Silver
10-482-4	.172	1/8	
10-482-5	.234	3/16	


10-452-X-05



RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)

NO	L	T	MATERIAL
10-452-3	.141	3/32	Brass
			FINISH Electro Solder/Copper


10-438-X-01



RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)

NO	L	T	MATERIAL
10-438-1	.078	1/32	Brass
10-438-2	.109	1/16	
10-438-3	.141	3/32	
10-438-4	.172	1/8	FINISH Silver
10-438-6	.234	3/16	
10-438-8	.297	1/4	


10-410-X-01



RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)

NO	L	T	MATERIAL
10-410-1	.075	1/32	Brass
10-410-2	.105	1/16	
10-410-3	.135	3/32	FINISH Silver
10-410-4	.165	1/8	


10-451-X-01



RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)


NO	L	T	MATERIAL
10-451-2	.109	1/16	Brass
10-451-3	.141	3/32	FINISH Silver
10-451-4	.172	1/8	

12-403-X-01




NO	L	T	MATERIAL
12-403-1	.075	1/32	Brass
12-403-2	.105	1/16	
12-403-3	.135	3/32	FINISH Silver
12-403-4	.165	1/8	

12-472-X-01



NO	L	T	MATERIAL
12-472-2	.105	1/16	Brass
12-472-3	.135	3/32	FINISH Silver
12-472-4	.165	1/8	


10-417-X-01



*FOR -1 ONLY IS .068

NO	L	T	MATERIAL
10-417-1	.078	1/32	Brass
10-417-2	.109	1/16	
10-417-3	.141	3/32	FINISH Silver
10-417-4	.172	1/8	
10-417-6	.234	3/16	
10-417-8	.297	1/4	


11-483-X-01



RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)


NO	L	T	MATERIAL
11-483-1	.075	1/32	Brass
11-483-2	.105	1/16	
11-483-3	.135	3/32	FINISH Silver
11-483-4	.165	1/8	

12-469-X-01



NO	L	T	MATERIAL
12-469-2	.105	1/16	Brass
12-469-3	.135	3/32	FINISH Silver
12-469-4	.165	1/8	


13-421-X-01



RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)

NO	L	T	MATERIAL
13-421-1	.075	1/32	Brass
13-421-2	.105	1/16	FINISH Silver
13-421-3	.135	3/32	
13-421-4	.165	1/8	


10-411-X-01



RECOMMENDED HOLE DIA
.116 DIA (#32 DRILL)

NO	L	T	MATERIAL
10-411-1	.078	1/32	Brass
10-411-2	.109	1/16	
10-411-3	.141	3/32	FINISH Silver
10-411-4	.172	1/8	
10-411-6	.234	3/16	


10-402-X-XX



RECOMMENDED MOUNTING HOLE
.116 DIA (#32 DRILL)

NO	L	T	MATERIAL
10-402-2	.109	1/16	Brass
10-402-3	.141	3/32	FINISHES
10-402-4	.172	1/8	(01) Silver (03) Gold/Copper

10-492-X-05



RECOMMENDED MOUNTING HOLE
.120 DIA (#31 DRILL)


NO	L	T	MATERIAL
10-492-1	.075	1/32	Brass
10-492-2	.105	1/16	FINISH
10-492-3	.135	3/32	Electro
10-492-4	.165	1/8	Solder/Copper

FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY

30 GREAT JONES STREET
NEW YORK, N.Y. 10012-1115
(212) 777-6571 • TWX 710-581-4930
FAX (212) 995-0161

TERMINALS


10-502-X-XX



RECOMMENDED MOUNTING
.076 DIA (#48 DRILL)

NO	L	T	MATERIAL	FINISHES
10-502-1	.051	1/32	Brass	(01) Silver
10-502-2	.082	1/16		(03) Gold/Copper
10-502-3	.113	3/32		(05) Electro-Solder
10-502-4	.145	1/8		
10-502-6	.207	3/16		
10-502-8	.270	1/4		


10-505-X-XX



RECOMMENDED MOUNTING HOLE
.094 DIA (#42 DRILL)

NO	L	T	MATERIAL	FINISHES
10-505-1	.062	1/32	Brass	(01) Silver
10-505-2	.094	1/16		(03) Gold/Copper
10-505-3	.125	3/32		
10-505-4	.156	1/8		


10-543-X-01



RECOMMENDED MOUNTING HOLE
.094 DIA (#42 DRILL)

NO	L	T	MATERIAL	FINISH
10-543-1	.062	1/32	Brass	Silver
10-543-2	.094	1/16		
10-543-3	.125	3/32		
10-543-4	.156	1/8		
10-543-6	.219	3/16		


10-503-X-XX



RECOMMENDED MOUNTING HOLE
.076 DIA (#48 DRILL)

NO	L	T	MATERIAL	FINISHES
10-503-1	.051	1/32	Brass	(01) Silver
10-503-2	.082	1/16		(03) Gold/Copper
10-503-3	.113	3/32		(05) Electro-Solder
10-503-4	.145	1/8		
10-503-6	.207	3/16		
10-503-8	.270	1/4		


13-554-X-01



RECOMMENDED MOUNTING HOLE
.094 DIA (#42 DRILL)

NO	L	T	MATERIAL	FINISH
13-554-1	.075	1/32	Brass	Silver
13-554-2	.105	1/16		
13-554-3	.135	3/32		
13-554-4	.165	1/8		


12-556-X-01



RECOMMENDED MOUNTING HOLE
.094 DIA (#42 DRILL)

NO	L	T	MATERIAL	FINISH
12-556-1	.075	1/32	Brass	Silver
12-556-2	.105	1/16		
12-556-3	.135	3/32		
12-556-4	.165	1/8		


11-559-X-01



RECOMMENDED MOUNTING HOLE
.094 DIA (#42 DRILL)

NO	L	T	MATERIAL	FINISH
11-559-1	.053	1/32	Brass	Silver
11-559-2	.084	1/16		
11-559-3	.115	3/32		
11-559-4	.147	1/8		


10-504-X-XX



RECOMMENDED MOUNTING HOLE
.094 DIA (#42 DRILL)

NO	L	T	MATERIAL	FINISHES
10-504-1	.062	1/32	Brass	(01) Silver
10-504-2	.094	1/16		(03) Gold/Copper
10-504-3	.125	3/32		
10-504-4	.156	1/8		


11-510-X-01



RECOMMENDED MOUNTING HOLE
.094 DIA (#42 DRILL)

NO	L	T	MATERIAL	FINISH
11-510-1	.075	1/32	Brass	Silver
11-510-2	.105	1/16		
11-510-3	.135	3/32		
11-510-4	.165	1/8		


13-533-X-01



RECOMMENDED MOUNTING HOLE
.094 DIA (#42 DRILL)

NO	L	T	MATERIAL	FINISH
13-533-1	.075	1/32	Brass	Silver
13-533-2	.105	1/16		
13-533-3	.135	3/32		
13-533-4	.165	1/8		


12-525-X-01



RECOMMENDED MOUNTING HOLE
.094 DIA (#42 DRILL)

NO	L	T	MATERIAL	FINISH
12-525-1	.053	1/32	Brass	Silver
12-525-2	.084	1/16		
12-525-3	.115	3/32		
12-525-4	.147	1/8		


10-541-X-05



RECOMMENDED MOUNTING HOLE
.094 DIA (#42 DRILL)

NO	L	T	MATERIAL	FINISH
10-541-2	.105	1/16	Brass	Silver
10-541-3	.135	3/32		
10-541-4	.165	1/8		


10-544-X-01



RECOMMENDED MOUNTING HOLE
.094 DIA (#42 DRILL)

NO	L	T	MATERIAL	FINISH
10-544-1	.082	1/32	Brass	Silver
10-544-2	.094	1/16		
10-544-3	.125	3/32		
10-544-4	.156	1/8		
10-544-6	.219	3/16		


10-542-X-01



RECOMMENDED MOUNTING HOLE
.094 DIA (#42 DRILL)

NO	L	T	MATERIAL	FINISH
10-542-1	.062	1/32	Brass	Silver
10-542-2	.094	1/16		
10-542-3	.125	3/32		
10-542-4	.156	1/8		
10-542-6	.219	3/16		

10-560-X-05



RECOMMENDED MOUNTING HOLE
.094 DIA (#42 DRILL)


NO	L	T	MATERIAL	FINISH
10-560-2	.105	1/16	Brass	Silver
10-560-3	.135	3/32		
10-560-4	.165	1/8		

FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY

30 GREAT JONES STREET
NEW YORK, N.Y. 10012-1115
(212) 777-6571 • 1-800-847-4162
FAX (212) 995-0161


TERMINALS

10-576-X-05




NO.	L	T	MATERIAL
10-576-2	.105	1/16	Brass
10-576-3	.135	3/32	
10-576-4	.165	1/8	
			FINISH
			Electro-Solder

12-511-X-01



PART NO.	L	T	MATERIAL
12-511-2	.105	1/16	Brass
12-511-3	.135	3/32	
12-511-4	.165	1/8	
12-511-6	.230	3/16	
			FINISH
			Silver


10-507-X-01



NO.	L	T	MATERIAL
10-507-1	.078	1/32	Brass
10-507-2	.109	1/16	
10-507-3	.141	3/32	
10-507-4	.172	1/8	
10-507-6	.234	3/16	
10-507-8	.297	1/4	
			FINISH
			Silver


*FOR-1 ONLY IS 073
RECOMMENDED MOUNTING HOLE
.185 DIA (#13 DRILL)

10-506-X-XX




NO.	L	T	MATERIAL
10-506-1	.062	1/32	Brass
10-506-2	.094	1/16	
10-506-3	.125	3/32	
10-506-4	.156	1/8	
10-506-6	.219	3/16	
			FINISHES
			(01) Silver
			(05) Electro-Solder

13-532-X-01




NO.	L	T	MATERIAL
13-532-1	.075	1/32	Brass
13-532-2	.105	1/16	
13-532-3	.135	3/32	
13-532-4	.165	1/8	
13-532-5	.195	5/32	
13-532-6	.230	3/16	
			FINISH
			Silver

12-515-X-01




NO.	L	T	MATERIAL
12-515-2	.105	1/16	Brass
12-515-3	.135	3/32	
12-515-4	.165	1/8	
12-515-5	.195	5/32	
12-515-6	.230	3/16	
			FINISH
			Silver

12-514-X-01




NO.	L	T	MATERIAL
12-514-1	.075	1/32	Brass
12-514-2	.105	1/16	
12-514-3	.135	3/32	
12-514-4	.165	1/8	
			FINISH
			Silver

10-562-X-03




NO.	L	T	MATERIAL
10-562-1	.075	1/32	Brass
10-562-2	.105	1/16	
10-562-3	.135	3/32	
10-562-4	.165	1/8	
10-562-5	.195	5/32	
10-562-6	.230	3/16	
			FINISH
			Gold

13-522-X-01



NO.	L	T	MATERIAL
13-522-2	.105	1/16	Brass
13-522-3	.135	3/32	
13-522-4	.165	1/8	
13-522-5	.195	5/32	
13-522-6	.230	3/16	
			FINISH
			Silver


10-513-X-01



NO.	L	T	MATERIAL
10-513-1	.075	1/32	Brass
10-513-2	.105	1/16	
10-513-3	.135	3/32	
10-513-4	.165	1/8	
10-513-6	.228	3/16	
10-513-8	.290	1/4	
			FINISH
			Silver


RECOMMENDED MOUNTING HOLE
.129 DIA (#30 DRILL)

13-530-X-05




NO.	L	T	MATERIAL
13-530-1	.075	1/32	Brass
13-530-2	.105	1/16	
13-530-3	.135	5/32	
13-530-4	.165	1/8	
13-530-5	.195	5/32	
13-530-6	.230	3/16	
			FINISH
			Electro Solder Plate

10-508-X-01



NO.	L	T	MATERIAL
10-508-1	.062	1/32	Brass
10-508-2	.094	1/16	
10-508-3	.125	3/32	
10-508-4	.156	1/8	
10-508-6	.219	3/16	
			FINISH
			Silver


10-512-X-XX



NO.	L	T	MATERIAL
10-512-1	.075	1/32	Brass
10-512-2	.105	1/16	
10-512-3	.135	3/32	
10-512-4	.165	1/8	
10-512-6	.228	3/16	
10-512-8	.290	1/4	
			FINISHES
			(01) Silver
			(05) Electro-Solder


RECOMMENDED MOUNTING HOLE
.129 DIA (#30 DRILL)

12-521-X-01



NO.	L	T	MATERIAL
12-521-2	.105	1/16	Brass
12-521-3	.135	3/32	
12-521-4	.165	1/8	
12-521-5	.195	5/32	
12-521-6	.230	3/16	
			FINISH
			Silver

12-550-X-01



NO.	L	T	MATERIAL
12-550-1	.075	1/32	Brass
12-550-2	.105	1/16	
12-550-3	.135	3/32	
12-550-4	.165	1/8	
12-550-5	.195	5/32	
12-550-6	.230	3/16	
			FINISH
			Silver


FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY

CONCORD
THE COMPONENT PEOPLE

30 GREAT JONES STREET
NEW YORK, N.Y. 10012-1115
(212) 777-8571 • TWX 710-581-4930
FAX (212) 995-0161


TERMINALS

09-0033-X-05




NO.	L	T	MATERIAL	FINISH
09-0033-1	.094	1/16	Brass	
09-0033-2	.125	3/32		Electro-Solder
09-0033-3	.156	1/8		

13-520-X-01



NO.	L	T	MATERIAL	FINISH
13-520-2	.105	1/16	Brass	Silver
13-520-3	.135	3/32		
13-520-4	.165	1/8		
13-520-5	.195	5/32		
13-520-6	.230	3/16		
13-520-8	.293	1/4		


10-615-X-05



* FOR -1 ONLY, THIS DIMENSION IS .047
RECOMMENDED MOUNTING HOLE .089 DIA (#43 DRILL)


NO.	L	T	MATERIAL	FINISH
10-615-1	.075	1/32	Brass	Electro Solder/Copper
10-615-2	.105	1/16		
10-615-3	.135	3/32		
10-615-4	.165	1/8		

10-526-X-01




NO.	L	T	MATERIAL	FINISH
10-526-2	.094	1/16	Brass	Silver
10-526-3	.125	3/32		
10-526-4	.156	1/8		

10-519-X-XX




NO.	L	T	MATERIAL	FINISHES
10-519-2	.094	1/16	Brass	(01) Silver
10-519-3	.125	3/32		(03) Gold/Copper
10-519-4	.156	1/8		
10-519-6	.219	3/16		
10-519-8	.281	1/4		

12-607-X-01



NO.	L	T	MATERIAL	FINISH
12-607-1	.075	1/32	Brass	Silver
12-607-2	.105	1/16		
12-607-3	.135	3/32		
12-607-4	.165	1/8		


10-509-X-XX



RECOMMENDED MOUNTING HOLE .204 DIA (#6 DRILL)

NO.	L	T	MATERIAL	FINISHES
10-509-2	.094	1/16	Brass	(01) Silver
10-509-3	.125	3/32		(05) Electro-Solder
10-509-4	.156	1/8		
10-509-6	.219	3/16		
10-509-8	.281	1/4		


10-601-X-XX



* FOR -1 ONLY, THIS DIMENSION IS .047
RECOMMENDED MOUNTING HOLE .094 DIA (#42 DRILL)


NO.	L	T	MATERIAL	FINISHES
10-601-1	.062	1/32	Brass	(01) Silver
10-601-2	.094	1/16		(03) Gold/Copper
10-601-3	.125	3/32		
10-601-4	.156	1/8		
10-601-6	.219	3/16		

13-603-X-01




NO.	L	T	MATERIAL	FINISH
13-603-1	.075	1/32	Brass	Silver
13-603-2	.105	1/16		
13-603-3	.135	3/32		
13-603-4	.165	1/8		

12-549-X-01




NO.	L	T	MATERIAL	FINISH
12-549-2	.105	1/16	Brass	Silver
12-549-3	.135	3/32		
12-549-4	.165	1/8		
12-549-5	.195	5/32		
12-549-6	.230	3/16		

13-606-X-01



NO.	L	T	MATERIAL	FINISH
13-606-1	.075	1/32	Brass	Silver
13-606-2	.105	1/16		
13-606-3	.135	3/32		
13-606-4	.165	1/8		


10-602-X-XX



RECOMMENDED MOUNTING HOLE .116 DIA (#32 DRILL)


NO.	L	T	MATERIAL	FINISHES
10-602-1	.078	1/32	Brass	(01) Silver
10-602-2	.109	1/16		(03) Gold/Copper
10-602-3	.141	3/32		
10-602-4	.172	1/8		
10-602-6	.234	3/16		
10-602-8	.297	1/4		

10-523-8-01




NO.	L	T	MATERIAL	FINISH
10-523-8	.281	1/4	Brass	Silver

12-605-X-01



NO.	L	T	MATERIAL	FINISH
12-605-1	.075	1/32	Brass	Silver
12-605-2	.105	1/16		
12-605-3	.135	3/32		
12-605-4	.165	1/8		

10-604-X-01



NO.	L	T	MATERIAL	FINISH
10-604-2	.109	1/16	Brass	Silver
10-604-3	.141	3/32		
10-604-4	.172	1/8		
10-604-6	.234	3/16		
10-604-8	.297	1/4		


FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY

CONCORD
THE COMPONENT PEOPLE

30 GREAT JONES STREET
NEW YORK, N.Y. 10012-1115
(212) 777-8571 • TWX 710-581-4930
FAX (212) 995-0161

TERMINALS

12-703-X-01




NO.	L
12-703-2	1/16
12-703-4	1/8
12-703-6	3/16
12-703-8	1/4
12-703-10	5/16

MATERIAL
Brass

FINISH
Silver

10-710-X-044



NO.	L	N	X	T
10-710-2	.094	.125	.031	1/16
10-710-3	.125	.156	.062	3/32
10-710-4	.156	.156	.094	1/8
10-710-6	.222	.156	.094	3/16
10-710-8	.285	.156	.094	1/4


RECOMMENDED MOUNTING HOLE
.144 DIA (#27 DRILL)

MATERIAL
Brass

FINISH
Bright Electro-Tin

MOUNTING: Hardware (Unassembled)
SCREW: Binding Head (Nickel Plated)
WASHER: Internal Tooth (Nickel Plated)


10-712-1-05



MATERIAL
Brass

FINISH
Electro Solder/Copper

12-704-X-01




NO.	L
12-704-3	3/32
12-704-4	1/8
12-704-6	3/16
12-704-8	1/4
12-704-10	5/16

MATERIAL
Brass

FINISH
Silver

13-714-X-01




NO.	L	T
13-714-1	.075	1/32
13-714-2	.105	1/16
13-714-3	.135	3/32
13-714-4	.165	1/8
13-714-5	.195	5/32
13-714-6	.230	3/16

MATERIAL
Brass

FINISH
Silver

10-709-3-01




RECOMMENDED MOUNTING HOLE
.129 DIA (#30 DRILL)

NO.	L	T
10-709-3	.125	3/32

MATERIAL
Brass

FINISH
Silver

10-706-X-XX




No.	L
10-706-4	.125
10-706-8	.188

MATERIAL
Brass

FINISHES
(01) Silver
(05) Electro-Solder

10-753-754-756-X-044



No.	A	B	C	D	H	J	L	N	P	Q	X	TAP	T
10-753-3	.312	.125	.068	.220	.172	.125	.141	.218	.062	.250	.117	6-32	3/32
10-754-4	.344	.141	.078	.250	.203	.156	.172	.250	.078	.312	.148	8-32	1/8
10-756-6	.375	.156	.094	.267	.203	.156	.234	.312	.093	.375	.190	10-32	3/16


MOUNTING HARDWARE (UNASSEMBLED)
SCREW BINDING HEAD (NICKEL PLATED)
WASHER INTERNAL TOOTH (NICKEL PLATED)

RECOMMENDED MOUNTING HOLE
10-753-3 .213 DIA (#3 DRILL)
10-754-4 .242 DIA (C DRILL)
10-756-6 .250 DIA (1/4 DRILL)

MATERIAL
Brass

FINISH
Bright
Electro-Tin

10-825-X-01




NO.	L	T
10-825-1	.075	1/32
10-825-2	.105	1/16
10-825-3	.135	3/32
10-825-4	.165	1/8

MATERIAL
Brass

FINISH
Silver

10-702-X-XX




NO.	L
10-702-4	.125
10-702-6	.188

MATERIAL
Brass

FINISHES
(01) Silver
(05) Electro-Solder

10-805-X-01




RECOMMENDED MOUNTING HOLE
.094 DIA (#42 DRILL)

NO.	L	T
10-805-1	.078	1/32
10-805-2	.109	1/16
10-805-3	.141	3/32
10-805-4	.172	1/8
10-805-6	.234	3/16
10-805-8	.297	1/4

MATERIAL
Brass

FINISH
Silver


10-707-1-01



MATERIAL
Brass

FINISH
Silver


10-711-1-05



MATERIAL
Brass

FINISH
Electro Solder/Copper

10-807-X-01



RECOMMENDED MOUNTING HOLE
.094 DIA (#42 DRILL)

NO.	L	T
10-807-1	.078	1/32
10-807-2	.109	1/16
10-807-3	.141	3/32
10-807-4	.172	1/8
10-807-6	.234	3/16
10-807-8	.297	1/4

MATERIAL
Brass

FINISH
Silver


FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY

CONCORD
THE COMPONENT PEOPLE

30 GREAT JONES STREET
NEW YORK, N.Y. 10012-1115
(212) 777-8571 • 1-800-847-4162
FAX (212) 995-0161

TERMINALS

10-806-X-01




NO	L	T
10-806-1	.078	1/32
10-806-2	.109	1/16
10-806-3	.141	3/32
10-806-4	.172	1/8
10-806-6	.234	3/16
10-806-8	.297	1/4

MATERIAL
Brass

FINISH
Silver

10-904-X-05




NO	L	T
10-904-1	.062	1/32
10-904-2	.094	1/16
10-904-3	.125	3/32
10-904-4	.156	1/8

MATERIAL
Brass

FINISH
Electro Solder Plate

10-905-X-05




NO	L	T
10-905-1	.062	1/32
10-905-2	.094	1/16
10-905-3	.125	3/32
10-905-4	.156	1/8

MATERIAL
Brass

ORDER AS 14-905-X-05 FOR COMMERCIAL BRONZE MATERIAL

FINISH
Electro Solder Plate

10-808-X-01




NO	L	T
10-808-1	.078	1/32
10-808-2	.109	1/16
10-808-3	.141	3/32
10-808-4	.172	1/8
10-808-6	.234	3/16
10-808-8	.297	1/4

MATERIAL
Brass

FINISH
Silver

14-946-X-05




NO	L	T
14-946-1	.062	1/32
14-946-2	.094	1/16
14-946-3	.125	3/32
14-946-4	.156	1/8

MATERIAL
Leaded Commercial Bronze

FINISH
Electro Solder/Copper

12-932-X-03




NO	L	T
12-932-1	.062	1/32
12-932-2	.094	1/16
12-932-3	.125	3/32
12-932-4	.156	1/8

MATERIAL
Brass

FINISH
Gold


10-8012-1-01 WIRE ADAPTER



MATERIAL
Brass

FINISH
Silver

12-931-X-03




NO	L	T
12-931-1	.062	1/32
12-931-2	.094	1/16
12-931-3	.125	3/32
12-931-4	.156	1/8

MATERIAL
Brass

FINISH
Gold

12-940-X-03




NO	L	T
12-940-1	.062	1/32
12-940-2	.094	1/16
12-940-3	.125	3/32
12-940-4	.156	1/8

MATERIAL
Brass

FINISH
Copper Strike/Gold

12-930-X-03




NO	L	T
12-930-1	.062	1/32
12-930-2	.094	1/16
12-930-3	.125	3/32
12-930-4	.156	1/8

MATERIAL
Brass

FINISH
Gold

14-947-X-05




NO	L	T
14-947-1	.062	1/32
14-947-2	.094	1/16
14-947-3	.125	3/32
14-947-4	.156	1/8

MATERIAL
Leaded Commercial Bronze

FINISH
Electro Solder/Copper

10-903-X-05




NO	L	T
10-903-1	.062	1/32
10-903-2	.094	1/16
10-903-3	.125	3/32
10-903-4	.156	1/8

MATERIAL
Brass

FINISH
Electro Solder Plate

10-939-X-05




NO	L	T
10-939-1	.052	1/32
10-939-2	.085	1/16

MATERIAL
Brass

FINISH
Electro Solder Plate

14-948-X-05




NO	L	T
14-948-1	.062	1/32
14-948-2	.094	1/16
14-948-3	.125	3/32
14-948-4	.156	1/8

MATERIAL
Leaded Commercial Bronze

FINISH
Electro Solder/Copper

10-914-X-05



NO	L	T
10-914-1	.062	1/32
10-914-2	.094	1/16
10-914-3	.125	3/32
10-914-4	.156	1/8

MATERIAL
Brass

FINISH
Electro Solder

FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY

30 GREAT JONES STREET
NEW YORK, N.Y. 10012-1115
(212) 777-6571 • TWX 710-581-4930
FAX (212) 995-0161