

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200895003](#)
Status: **Active**
Overview: [Brad Nano-Change \(M8\) Products](#)
Description: Y Nano-Change (M8) Splitter to Nano-Change (M8) 4 Pole Female to 4 Pole Male

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Industrial Tees and Splitters
 Series [120089](#)
 IP Rating IP67
 Overview [Brad Nano-Change \(M8\) Products](#)
 Product Name Nano-Change (M8)
 Type Splitter - Solid Body
 UPC 883906319472

Physical

Drop Connector Nano-Change (M8)
 Drop Gender Male
 Keyway None
 Left Trunk Connector Nano-Change (M8)
 Left Trunk Gender Female
 Leg 1 Length N/A
 Leg 2 Length N/A
 Material - Cable Jacket N/A
 Material - Connector Body PUR
 Material - Coupling Nut Nickel-plated Brass
 Net Weight 1.000/g
 Poles 3
 Right Trunk Connector Nano-Change (M8)
 Right Trunk Gender Female
 Temperature Range - Operating -20°C to +90°C

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum 60V AC / 75V DC

Material Info

Engineering Number 0808 04LMF 00001

Reference - Drawing Numbers

Sales Drawing SD-120089-002

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[120089](#) Series