

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1210400140](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Valve Connector, Form A - 18mm, 2 Pole Plus Ground Position H6/H12, to 1.0m (3.28') PVC Cable Pigtail, Black Nitrile Gasket, 250V

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E218123

General

Product Family Industrial Cordsets
 Series [121040](#)
 Connector End A Brad mPm DIN A - 18mm
 Connector End B Pigtail
 IP Rating IP65
 Material - Contact Brass
 Overview [mPm DIN Valve Connectors](#)
 Product Name mPm
 Protocol N/A
 Region America, Europe
 Type Single Ended
 UPC 883906361488

Physical

Cable Diameter 5.72mm (.225")
 Cable Length 1.0m (3.28')
 Color - Cable Jacket Black
 Coupling Style Threaded
 Gender Male-Pigtail
 Keyway None
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body Polypropylene
 Material - Coupling Nut N/A
 Material - Plating Mating Gold
 Net Weight 26.050/g
 Orientation 90° to Pigtail
 Poles 2
 Temperature Range - Operating -40°C to +90°C
 Wire Size AWG N/A
 Wire/Cable Type N/A

Electrical

Current - Maximum per Contact 5.0A
 Voltage - Maximum 250V

Material Info

Engineering Number E152N3N10011

Reference - Drawing Numbers

Sales Drawing 1210400050-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[121040 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION