

[Skip to content](#)



Our commitment. Your advantage.



• [Products](#)

- [By Type](#)
 - [Connectors](#)
 - [Electromechanical Components](#)
 - [Electronic Modules](#)
 - [Fiber Optics](#)
 - [Filters](#)
 - [Identification & Labeling](#)
 - [Passive Components](#)
 - [Power Sources](#)
 - [RF & Microwave Products](#)
 - [Tooling Products](#)
 - [Touch Screen Displays](#)
 - [Tubing, Molded and Harnessing Products](#)
 - [Wire, Cable and Cable Assemblies](#)
 - [List all product types...](#)
- [By Industry](#)
 - [Aerospace & Defense Products](#)
 - [Appliance](#)
 - [Automotive](#)
 - [Communications](#)
 - [Computer & Consumer Electronics](#)
 - [Industrial & Commercial](#)
 - [Instrumentation & Medical](#)
- [By Brand](#)
- [A to Z](#)
- [Product News](#)

• [Documentation](#)

- [Find Documents & Drawings](#)
- [Find CAD Models](#)
- [SPICE/Electrical Models](#)
- [NAFTA Certificate of Origin](#)
- [White Papers](#)

• [Resources](#)

- [RoHS Compliance & Alternates](#)
- [Cross Reference Products](#)
- [Compare Multiple Products](#)
- [Check Distributor Inventory](#)
- [Find Authorized Distributors](#)

• [My Account](#)

- [Sign In](#)
- [Register](#)

• [Customer Support](#)

- [Support](#)
- [RoHS Support Center](#)
- [Glossary of Terms](#)
- [eBulletin Newsletter](#)

MRJB4304 Product Details





MRJB4304



Active

Rotary Switches



[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Number of Positions = 3
- Angle of Throw = 30.00
- Actuator Style = Screwdriver/Coin
- Code Type = 4 Poles
- Straight Mount Angle

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Compare Products](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [ROTARY SWITCH 12 POSITION-30%DETENT](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Number of Positions](#) = 3
- [Angle of Throw \(°\)](#) = 30.00
- [Actuator Style](#) = Screwdriver/Coin
- [Code Type](#) = 4 Poles
- [Mount Angle](#) = Straight
- Product Series = MRJB
- Comment = Process Sealed - Splash proof; Fixed

Electrical Characteristics:

- Contact Rating = 0.4VA

Termination Related Features:

- Solder Tail Contact Plating = Gold over Nickel

Contact Related Features:

- Contact Material = Brass

Housing Related Features:

- Housing Material = Die Cast Zinc

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240C, Wave solder capable to 265C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Alcoswitch

[Provide Website Feedback](#) | [Contact Customer Support](#)

[Home](#) | [Customer Support](#) | [Suppliers](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)

2008 Tyco Electronics Corporation All Rights Reserved