




Our commitment. Your advantage.

- [Products](#)
- [Documentation](#)
- [Resources](#)
- [My Account](#)
- [Customer Support](#)

[Home](#) > [Products](#) > [By Type](#) > [Resistors](#) > [Product Feature Selector](#) > Product Details

## 404806411009 Product Details

[Live Product Chat](#)



**404806411009**  
(1623849-9)

TE Internal Number: 1623849-9

[Active](#)

### Variable Resistors

[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Variable Resistor
- Resistor Type = Trimmer
- Resistance Selection = K ?
- Resistance = 5K ?
- Power Rating = .50 W

[View all Features](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

- [Add to My Part List](#)
- [Request Sample](#)
- [Find Similar Products](#)
- [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [PROFESSIONAL TRIMMERS SERIES 4290W](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- [Professional Trimmers - Type 4290 Series - Tyco Elec...](#) (PDF, English)

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Variable Resistor
- [Resistor Type](#) = Trimmer
- [Resistance \(?\)](#) = 5K
- [Element](#) = Cermet
- [Sealed](#) = Yes
- [Mount Angle](#) = Horizontal
- [Termination Type](#) = PCB Terminations

#### Electrical Characteristics:

- Resistance Selection (?) = K
- [Power Rating \(W\)](#) = 0.50
- [Tolerance \(%\)](#) = 10

#### Termination Related Features:

- [Termination Post Orientation](#) = In Line

#### Body Related Features:

- [Series](#) = 4290
- [Package, Component Size](#) = 10

#### Configuration Related Features:

- [Sections](#) = Single
- [Adjustment Location](#) = Top
- [Adjustment Style](#) = Screwdriver Slot
- [Operating Function](#) = Multi Turn

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

#### Conditions for Usage:

- [Temperature Coefficient \(ppm/°C\)](#) = 100

#### Other:

- Brand = Citec

[Provide Website Feedback](#) | [Need Help?](#)