

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT – BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST
H	—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	WO 00/7012	20-07-00	—	VS
	B	SR10-0250-02	24-05-02	—	BC
	B1	ECR-09-015706	24-11-09	AEG	MKO







Loading Pattern (8 contacts)

	1	2	3	4	5	6	7
Row a	+	o	+	o	+	o	+
Row b	o	o	o	o	o	o	o
Row c	+	o	+	o	+	o	+


\+ = contact
o = no contact





Specifications acc. IEC 603-2. Performance Level 2

Housing :	PBTP 30% Glasfilled (UL94-V0) Pebblegrey similar RAL 7032
Contact material : Plating :	Copper Alloy Contact area : PdNi+Au or Au Termination area : Sn with flux-thight coating.



1) Center-displacement between termination- and contact-side.

Active Partnumber. Contact Tyco Electronics for other configuration availability

Old Partnumber	TE Partnumber
V42254-F2299-R1	1393657-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL –
FINISH –

DWN Cuvelier 10JUN98
CHK —
APVD PD COM
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —

Tyco Electronics Corporation
's-Hertogenbosch, Nederland

NAME Receptacle Ass'y, Type R, 21 pos.
V42254-F2299-R1-*-26

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-1393657-1	—

CUSTOMER DRAWING | SCALE 5:1;10:1 | SHEET 1 OF 1 | REV B1

1393657-1