




TWINAX & TRIAX CONNECTORS



Active

PRODUCT DRAWING
English

3D PDF

TE CONNECTIVITY (TE) TWIN VIDEO PLUG

227241-1
TE Internal Number: 227241-1

Always EU RoHS/ELV Compliant

Applies To **Coaxial Cable**

Cable Termination Method **Crimp**

50 Ohm **No**

75 Ohm **No**

RF Connector Type **Twinax**

Product Drawings

[PLUG, SERIES TWIN](#)
PDF (TIFF AVAILABLE)
English

[PLUG, SERIES TWIN](#)
PDF (TIFF AVAILABLE)
English

CAD Files

[Customer View Model](#)
2D_DXF.ZIP
English

[Customer View Model](#)
3D_IGS.ZIP
English

[Customer View Model](#)
3D_STP.ZIP
English

[3D PDF](#)
PDF
English

Product Specifications

Product Specification

[Connector, TWINAX, Plugs And Receptacles](#)
PDF
English

[Connector, TWINAX, Plugs And Receptacles](#)
TIF
English

Instruction Sheets

Instruction Sheet (U.S.)

[Twin Video Plug](#)
PDF
English

[Twin Video Plug](#)
TIF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Applies To	Coaxial Cable
	RF Connector Type	Twinax
	Connector Style	Plug
	Cable Type	IBM 7362229 B
	Dielectric Material	Polyester
	Product Type	Connector - RF

Electrical Characteristics	50 Ohm	No
	75 Ohm	No

Body Features	Body Style	Straight
	Body Plating Material	Nickel
	Body Material	Zinc

Contact Features	Center Contact Material	Brass
	Center Contact Plating Material	Silver

Termination Features	Cable Termination Method	Crimp
----------------------	--------------------------	--------------

Mechanical Attachment	Panel Mount	Without
	Coupler Style	Threaded
	Mating Alignment	With
	Mating Alignment Type	Keyed

Product Compliance [Statement of Compliance](#)
PDF

[VIEW ALL PRODUCT COMPLIANCE](#)