

1825008-6 ✓ ACTIVE

[Alcoswitch](#) | [Alcoswitch DIP](#), [Alcoswitch Rotary DIP DRM](#)

TE Internal #: 1825008-6

Alcoswitch DIP, Rotary Switches, 10 Position, Mini-Plastic Shaft

Actuator Style, Rotary Switch Style, Rotary DIP Rotary Switch Type,
10 Switch

[View on TE.com >](#)



[Relays, Contactors & Switches](#) > [Switches](#) > [Rotary Switches](#)



Number of Rotary Switch Positions: 10

Actuator Style: **Mini-Plastic Shaft**

Switch Style: **Rotary**

Rotary Switch Type: **Rotary DIP**

Number of Switches: 10

Features

Product Type Features

Removable Tape Seal	Without
Product Type	Switch
Illuminated	No
Actuator Style	Mini-Plastic Shaft
Switch Style	Rotary
Rotary Switch Type	Rotary DIP
Sealed Rotary Switch	No
Code Type	BCD

Configuration Features

Number of Rotary Switch Positions	10
Number of Switches	10

Electrical Characteristics

Rotary Switch Voltage Rating	20 VAC
------------------------------	--------

Contact Features

Solder Tail Contact Plating	Gold Flash over Nickel
Rotary Switch Contact Current Rating	.4 A
Rotary Switch Contact Mating Area Plating Material	Gold Flash
Contact Base Material	Copper Alloy



Termination Features

Termination Style	Printed Circuit Board
-------------------	-----------------------

Mechanical Attachment

Rotary Switch Mounting Type	Through Hole
Rotary Switch Mounting Angle	Right Angle

Housing Features

Centerline	2.54 mm[.1 in]
Rotary Switch Housing Material	Thermoplastic

Usage Conditions

Oil-Tight	No
-----------	----

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tube
------------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JUN 2016 (169) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Model / Part # 1825008-8
DRM16RA04=Rot Dip,R/A



TE Model / Part # 1-1825033-1
DRM1604=Rot Dip,w/Knurled Shaf



TE Model / Part # 1825033-1
DRM10E04=Rot Dip,w/Knurled Shaf

Also in the Series | Alcoswitch DIP



DIP & SIP Switches(256)



Rotary Switches(34)



Switch Boots & Accessories(1)

Also in the Series | Alcoswitch Rotary DIP DRM



Rotary Switches(2)


Customers Also Bought




TE Model / Part #1825008-8
DRM16RA04=Rot Dip,R/A




TE Model / Part #3-647502-6
06P MTA100 SMT ASSY,SN,TAPE, LF



TE Model / Part #5353999-5
0.8FH,R05H.5,120,30/Sn,TR,SC



TE Model / Part #533082-3
HDI KEYING POWER PIN PLTD



TE Model / Part #1-1623790-0
SQM10S 100R 5% LP (WIRE)



TE Model / Part #1676362-3
RN 0805 4K87 0.1% 10PPM 5KRL



TE Model / Part #1-1879501-8
CRGH2512 5% 5R1 2W



TE Model / Part #1802162-3
1-PORT MATENET HDR 90DEG
SEALED, COD C



TE Model / Part #3-641121-6
06P MTA156 HDR ASSY FL/RA LF



TE Model / Part #5-146503-3
06 MODII HDR DRST UNSHRD STKG

Documents

Product Drawings

DRM10RA04=Rot Dip,R/A

English

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English