

1-1337495-0 Product Details



1-1337495-0

TE Internal Number: 1-1337495-0

[Active](#)

BNC RF Connectors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector - RF
- Plug
- Connector Style = Plug
- Applies To Coaxial Cable
- Coaxial Cable Termination Type = Crimp

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Have a Question?

Chat with a Product Information Specialist



Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [BNC STRAIGHT PLUG CRIMP 75 OHM BT2002 \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector - RF
- Gender = Plug
- [Crimp Type](#) = Hex
- [Body Style](#) = Straight
- [Grade](#) = Professional
- [Body Material](#) = Brass
- [Sealed](#) = No
- [Isolated](#) = No
- [Dielectric Material](#) = PTFE
- [Coupling Nut Material](#) = Brass
- Number of Ports = 1
- Gasket Material = White Silicone Rubber

Mechanical Attachment:

- Surface Mountable = No
- Panel Attachment = Without

Electrical Characteristics:

- [Connector Impedance \(Ω\)](#) = 75
- Frequency = DC - 2 GHz

Termination Related Features:

- [Coaxial Cable Termination Type](#) = Crimp

Body Related Features:

- [Hardware Included](#) = No
- [Body Plating](#) = Nickel
- [Polarized](#) = No
- Ferrule Type = Hex
- Hand Tool No. = 9-1478240-0
- Interchangeable Die Set Number = 9-1478242-0
- Crimp Dimensions = 1.75 + 2.6 + 5.6 + 6.5

Contact Related Features:

- [Center Contact Material](#) = Brass
- [Center Contact Plating](#) = Gold

Housing Related Features:

- Connector Style = Plug

Configuration Related Features:

- [Coaxial Cable Type \(RG/U or Mfg.\)](#) = BT2002

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Applies To](#) = Coaxial Cable
- Operating Temperature (Max.) (°C) = 165

Packaging Related Features:

- Packaging Method = Individual
- Packaging Quantity = 50

Other:

- Brand = Greenpar

[BOOKMARK](#)

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

