

1825259-2 Product Details

[Share](#) [Print](#) [Email](#)


1825259-2
(MSS1300G04)

TE Internal Number: 1825259-2

[Active](#)

Slide Switches

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- 3 Positions
- Single Pole - Three Throw Configuration (Pole-Throw)
- Actuator Style = Top
- Actuator Color = Black
- MSS Series

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [SLIDE SWITCH, MSS 1300 SERIES, SP-3T, VERTICAL](#) (PDF, English)

Catalog Pages/Data Sheets:

- [SWITCHES CORE PROGRAM CATALOG](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Configuration (Pole-Throw) = Single Pole - Three Throw
- Actuator Style = Top
- Series = MSS
- Mount Angle = Vertical
- Terminal Configuration = Standard
- Grade = Instrumentation
- Termination Type = PC
- PCB Mount Retention = With

Electrical Characteristics:

- Contact Rating = 0.4 VA max @ 20 VDC or peak AC

Body Features:

- [Number of Positions](#) = 3
- Actuator Color = Black
- Mount Style = Through-Hole
- PCB Tail Length (mm [in]) = 3.80 [0.150]
- PCB Mount Retention Type = Guide Posts
- Actuator Length (mm [in]) = 8.51 [0.335]
- Actuator Material = POM
- Actuator Travel = 2.00 [.079]

Contact Features:

- Contact Plating = Gold

Housing Features:

- UL Flammability Rating = UL 94-HB

Configuration Features:

- Threaded Case = With
- Number of Actuators = Single

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Identification Marking:

- Stamped Marking = With

Other:

- Brand = Alcoswitch

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

