




Ansicht "X"
VIEW

1

Formbedingter Verzug von 0.4mm zulaessig
MOULD DEPENDING WARE PAGE OF 0.4MM PERMITTED

2

Verwendet mit Gehaeuse
966 906 (ASSY 966 908)
966 907 (ASSY 966 909)

USED WITH HOUSING
966 906 (ASSY 966 908)
966 907 (ASSY 966 909)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.
DIESES ZEICHNUNGSDOKUMENT WIRD DURCH AMP INCORPORATED KONTROLLIERT.
ÄNDERUNGEN, DIE DEN TECHNISCHEN FORTSCHRITT DIENEN, SIND VORBEHALTEN.
DEN JEWEILS LETZTQUELTIGEN ÄNDERUNGSSTAND ERFAHREN SIE AUF ANFRAGE.

DIMENSIONS:
DIMENSIONEN:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED,
ALLGEMEINTOLERANZEN

n. DIN 16901 - 140

ANGLES /WINKEL ±2°
FINISH /OBERFLÄCHE/FARBE

PBT-GF
schwarz/BLACK

DWN
D. Dünkel
05-MAR-97

CHK
B. KIRSCH
06-MAR-97

APVD
-

PRODUCT SPEC
PRODUKTSPEZ.
-

APPLICATION SPEC
VERARBEITUNGSSPEZ.
-

WEIGHT
GEWICHT
-

05-MAR-97

06-MAR-97

-

-

-

-

NAME
LOCKING COVER FOR MODU MT PIN-AND TSMT REC.HSG., 2X3POSN.
Verrriegelungsdeckel fuer Modu MT Stift-und TSMT Bu.-Geh., 2x3pol.

SIZE
A3

CAGE CODE
00779

DRAWING NO
ZEICHNUNGS-NR.
C-964 967

RESTRICTED TO
NUR FÜR
VW/AUDI

CUSTOMER DRAWING
/KUNDENZEICHNUNG

MASSSTAB 2:1

BLATT 1

OF 1

REV B

AMP 1470-19 REV 27JUN96

05-MAR-97 10:35:32 eg004311 /home/eg004311/edmod