


NUMBER
280677

⚠ LUNGHEZZA DI DORATURA SELETTIVA PER P.N. 280677-2-3

OTTONE	0,0015 MIN. DORATURA SELETT. + 0,0030 FLASH SU 0,0012 MIN. NICKEL	280677-3
T4	0,0015 MIN. DORATURA SELETT. SU 0,0012 MIN. NICKEL	280677-2 ← OBSOLETE
MATERIALE	FINITURA SUPERFIC.	AMP P.N.



2) RESTRICTED -
NOT FOR SALES
OUTSIDE ITALY

DIMENSIONS IN MM. DO NOT SCALE PRINT

G REVISED PERECU ET00-0176-94				© 1975 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.				CUSTOMER COPY REFERENCE ONLY			
F REVISIONATO				MATERIAL AND FINISH				AMP ITALIA VIA CERVI 15 COLLEGNO (TORINO)			
D AGGIUNTA NOTA 2				VEDERE TABELLA				CLASS			
C REVISIONATO				WIRE RANGE INSULATION				TYPE			
B CANCELLATO -4				05-1 mm2				SCALE			
A IN PRODUZIONE				TOLERANCE EXCEPT AS NOTED				LOC NO			
LTR REVISION RECORD				DATE				A 280677			
DE 1-12-75				APP				REV G			
CHK 1st dec 75				NAME CONTATTO A LINGUETTA SINGOLA PER CONNETTORE F.S.							

PRINT DIST