
Subminiature D Connectors for Cable Mounting (Continued)

Standard Density Solder Cup Termination

Industrial



Material and Finish:

Front Shell—Steel, tin plated
Housing—Grey thermoplastic PBTP
Flammability—UL 94V-0
Contact Material—Copper alloy
Contact Area Plating—Nickel/Pd/Gold (>250 mating cycles)
Current Rating—3A
Insulation Resistance—5000 MΩ min.
Dielectric Strength—1000V AC min.
Temperature Rating—-55°C to +125°C


Plug Connector

No of Ways	Part Number
9	3-1393483-8
15	3-1393483-9
25	4-1393483-0
37	4-1393483-1

Socket Connector

No of Ways	Part Number
9	4-1393483-7
15	4-1393483-8
25	4-1393483-9
37	5-1393483-0

Commercial



Material and Finish:

Front Shell—Steel, tin plated
Housing—Black glass-filled thermoplastic
Flammability—UL 94V-0
Contact Material—Copper alloy
Contact Area Plating—Gold
Current Rating—5A
Insulation Resistance—500 MΩ min.
Dielectric Strength—1000V AC min.
Temperature Rating—-40°C to +105°C

Plug Connector

No of Ways	Part Number
9	344642-1
15	344644-1
25	344646-1
37	344651-1

Socket Connector

No of Ways	Part Number
9	344643-1
15	344645-1
25	344647-1
37	344652-1

Catalog 82068
Revised 3-04

www.tycoelectronics.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752
Canada: 1-905-470-4425
Mexico: 01-800-733-8926
C. America: 52-55-5-729-0425

South America: 55-11-3611-1514
Hong Kong: 852-2735-1628
Japan: 81-44-844-8013
UK: 44-141-810-8967