







P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	ECR-20-017513	06JAN2021	E.Z	N.S

AS SHOWN : 1759392-1



1. MATERIAL
 ① HSG : HIGH TEMP, THERMOPLASTIC, UL94V-0, BLACK
 ② CONTACT : COPPER ALLOY
 FINISH ;
 CONTACT AREA : Au PL. OVER Ni UNDER PL.
 SOLDERING AREA : Au PL. OVER Ni UNDER PL.
 ③ SHELL : COPPER ALLOY
 FINISH ; Tin PL. OVERALL
 GENERAL TOLERANCE OF CONNECTOR: ±0.2, ±1°
 ③ NON CUMULATIVE



RECOMMENDED PWB LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.CHIEN 29NOV06	TE Connectivity Ltd.			
DIMENSIONS: mm		CHK K.KOBAYASHI 29NOV06				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD W.KODAMA 29NOV06	NAME 0.8MM PITCH 20POS. WIRE TO BOARD RECEPTACLE CONNECTOR ON BOARD TYPE			
0 PLC ±		PRODUCT SPEC 108-99004	SIZE	CAGE CODE	DRAWING NO	
1 PLC ±		APPLICATION SPEC	A3	00779	C-1759392	
2 PLC ±		MATERIAL	WEIGHT	RESTRICTED TO		
3 PLC ±		FINISH	CUSTOMER DRAWING	SCALE	SHEET	REV
4 PLC ±			4:1	1 OF 2	B2	
ANGLES ±						

