






DRAWING MADE IN THIRD ANGLE PROJECTION  
 THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

LOC		DIST		P		F		ZONE		LTR		REVISIONS		DATE	APPD	
FT													DESCRIPTION			
													E	REV; EC 0502-0084-96	05NOV96	DH
													F	REV PER EC 0320-138-97	30 APR 97	GJ
													G	REV PER EC 063C-169-02	23 JUL 02	KW

- RECEPTACLE ACCEPTS A 0.20-0.36 [.008-.014] THICK I.C. LEAD.
- TUBE LOADED.



SECTION A-A  
SCALE 10:1



RECOMMENDED MOUNTING HOLE PATTERN  
SCALE 4:1

GOLD	PHOS. BRZ	BLACK GLASS-FILLED PCT UL94V-0	2-382761-4
TINNED	PHOS. BRZ	BLACK GLASS-FILLED PCT UL94V-0	2-382761-3
CONTACT FINISH	CONTACT MAT'L	HOUSING MATERIAL	PART NO.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON :		DR	3-25-93	AMP INCORPORATED Harrisburg, Pa. 17105	
2 PL DEC ±-		P. COLLINS	3-25-93	NAME SOCKET ASSY, DIP, OTC, HT, SHORT LEG, 28 POS, DIPLOMATE DL	
3 PL DEC ±0.13 [.005]		CHK	3-25-93		
ANGLES ±-		R. TALLEY	3-25-93		
		APPD	3-25-93		
MATERIAL	SEE TABLE	F. BOYD	3-25-93	SIZE <b>D</b> 00779	
FINISH	SEE TABLE	L. STEPHENS	3-25-93		
		PRODUCT SPEC	108-1066	SCALE 5:1	
		APPLICATION SPEC	114-1052		
		WEIGHT	-	CUSTOMER DRAWING	