


REVISONS		DATE	DWN	APVD
REV	DESCRIPTION			
S	REV PER ECO 10-024292	12-1-10	CT	KT



MAT'L: LEADED COPPER PER ASTM-B-301  
 FINISH: GOLD PLATED .000050 MIN THK  
 PER ASTM-B-488 OVER NICKEL PLATE  
 .000050 MIN THK PER AMS-QQ-N-290

REMARKS	DIM G	DIM F	PART NUMBER
1	.776	.079-.083	3-448140-0
1 3	.617±.010	.087 MAX	2-448140-7
1	.576	.079-.083	2-448140-6
1 3 5	.617	.087 MAX	2-448140-3
1	.606	.079-.083	2-448140-2
1 3	.651	.087 MAX	1-448140-9
1	.505	.079-.083	1-448140-8
1	.617	.079-.083	1-448140-5
1	.404	.079-.083	1-448140-2
3	.536	.087 MAX	448140-9
--	.415	.079-.083	448140-8
1	.651	.079-.083	448140-6
1	.536	.079-.083	448140-3
--	.536	.079-.083	448140-2

- 1 COLOR CODE: AS SHOWN IN APPROXIMATE LOCATION SHOWN. THE YELLOW BAND SHALL BE APPROXIMATELY TWICE THE WIDTH OF THE ORANGE BAND.
- 2 ELECTRICAL ENGAGEMENT POINT.
- 3 THIS AREA SOLDER DIPPED.
- 4 MANUFACTURERS LOGO; LACATION & ORIENTATION OPTIONAL.
- 5 SOLDER IS RoHS-COMPLIANT Sn.

DIMENSIONS: INCHES TOLERANCES UNLESS OTHERWISE SPECIFIED: 9 PLC ± 3 PLC ± 5 PLC ±.005 4 PLC ± ANGLES ± FINISH SEE CALLOUTS		DWN C.C. THOMAS 27OCT2009 CHK K. THACKSTON 27OCT2009 APVD K. THACKSTON 27OCT2009 PRODUCT SPEC APPLICATION SPEC WEIGHT CUSTOMER DRAWING	Tyco Electronics Harrisburg, PA 17105-3608 NAME POSTED PIN CONTACT, SIZE 12, ARINC 600 SIZE CAGE CODE DRAWING NO A100779C=448140 SCALE 12:1 SHEET 1 OF 1 REV S
---	--	--	--