

# BFMSUBD-15M-ANA-S



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → PLC Wiring Systems  
→ PLC Connecting Interfaces

## General Information

<b>Extended Product Type:</b>	BFMSUBD-15M-ANA-S
<b>Product ID:</b>	1SNA021061R1000
<b>EAN:</b>	3472590210614
<b>Catalog Description:</b>	BFMSUBD-15M-ANA-S - Connecting Interface
<b>Long Description:</b>	BFSUBD Interruptible two wire interface with subd 15 male poles connector.

## Ordering

<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	85371098

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNC127001C0206
<b>Instructions and Manuals:</b>	1SNC127001C0206

## Dimensions

<b>Product Net Width:</b>	90 mm
<b>Product Net Height:</b>	104 mm
<b>Product Net Depth / Length:</b>	71.3 mm
<b>Product Net Weight:</b>	0.280 kg

## Technical

<b>Connection Type:</b>	Pluggable - Screw clamp
<b>Pollution Degree:</b>	2
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Wire Stripping Length:</b>	7.5 mm
<b>Recommended Screw Driver:</b>	3.5 mm

## Technical UL/CSA

<b>Connecting Capacity UL/CSA:</b>	Stranded 14 AWG
<b>Flammability According to UL94:</b>	V0

## Certificates and Declarations (Document Number)

<b>Declaration of Conformity - CE:</b>	1SND225028U1000
--	-----------------

---

<b>Environmental Information:</b>	1SNC127001C0207_Ch_A
-----------------------------------	----------------------

---

<b>Instructions and Manuals:</b>	1SNC127001C0206
----------------------------------	-----------------

---

## Classifications

<b>Object Classification Code:</b>	X
------------------------------------	---

---

<b>ETIM 4:</b>	EC001604 - Fieldbus, decentr. periphery - communication module
----------------	--

---

<b>ETIM 5:</b>	EC002780 - Interface module
----------------	-----------------------------

---

<b>ETIM 6:</b>	EC002780 - Interface module
----------------	-----------------------------

---

## Container Information

<b>Package Level 1 Units:</b>	1 piece
-------------------------------	---------

---

<b>Package Level 1 Width:</b>	147 mm
-------------------------------	--------

---

<b>Package Level 1 Depth / Length:</b>	117 mm
--	--------

---

<b>Package Level 1 Height:</b>	97 mm
--------------------------------	-------

---

<b>Package Level 1 Gross Weight:</b>	0.28 kg
--------------------------------------	---------

---

<b>Package Level 1 EAN:</b>	3472590210614
-----------------------------	---------------

---

<b>Package Level 2 Units:</b>	15 piece
-------------------------------	----------

---

<b>Package Level 2 Width:</b>	300 mm
-------------------------------	--------

---

<b>Package Level 2 Depth / Length:</b>	500 mm
--	--------

---

<b>Package Level 2 Height:</b>	300 mm
--------------------------------	--------

---

<b>Product Packing Type:</b>	Box
------------------------------	-----

---