



## T14-23FR Product Details

[Share](#) | [Print](#) | [Email](#)


**T14-23FR**

TE Internal Number: 193578-001

Active

### Molded Parts

Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- Molded Part Type = Break-out
- Family Name = T
- Transition Type = Break-out
- 3 Branches/Legs
- General Purpose Application

[View all Features](#)

### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [Cable Breakout Boot, Three Entry \(PDF, English\)](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Molded Part Type = Break-out
- Family Name = T
- Adhesive Description = Good Water Blocking Pre-Coat Adhesive
- Size = 14-23

#### Mechanical Attachment:

- Adhesive Pre-Coating = With

#### Dimensions:

- 1st Branch/Leg Range (mm [in]) = 4.57 - 12.70 [0.180 - 0.500]
- 2nd Branch/Leg Range (mm [in]) = 4.57 - 12.70 [0.180 - 0.500]
- 3rd Branch/Leg Range (mm [in]) = 4.57 - 12.70 [0.180 - 0.500]

#### Body Features:

- Transition Type = Break-out
- Material = Semi rigid Modified Polyolefin

#### Housing Features:

- Max. Inside Diameter of Part (mm [in]) = 17.78 - 30.48 [0.700 - 1.200]

#### Configuration Features:

- Number of Branches/Legs = 3
- Material Code = 3

#### Industry Standards:

- Government/Industry Qualification = No
- Approved Standards = MIL-I-81765/1A
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Environmental:

- Operating Temperature (°C) = -55 - +90

#### Operation/Application:

- Application = General Purpose

#### Purchasing Information:

- Adhesive Code = 97

#### Other:

- Brand = Raychem

### Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

### Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

