



CONNECTORS

SCREENED



✓ Active

TE CONNECTIVITY (TE)

208M916-19B08

Raychem | Magnaform Backshells

208M916-19B08

TE Internal Number: 937237-000

Alias ID: 8-1197260-9

Not EU RoHS Compliant

Not EU ELV Compliant

Cable Diameter Range 64 – 102 mm [25 – 4 in]

Adapter Entry Size 08

Material Aluminum

Adapter Plating Material Cadmium per SAE AMS-QQ-P-416, Type II, Class 3, over appropriate under plate, per SAE AS85049 (500

Hour Salt Spray)

Style Shielded Boot

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings

Braid Tail Backshell

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Style Shielded Boot

Termination Device Type Magneform Ring

Body Features

Adapter Entry Size 08

Material Aluminum

Adapter Plating Material Cadmium per SAE AMS-QQ-P-416, Type II, Class 3, over appropriate under plate, per SAE AS85049 (500 Hour Salt Spray)

Dimensions

Cable Diameter Range 64 – 102 mm [25 – 4 in]

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
