

SETR16AI-TINEL-LOCK-RING Product Details

[Share](#) | [Print](#) | [Email](#)


Active

Side Entry Tinel-Lock Rings

SETR16AI-SIDE-ENTRY-TINEL-LOCK-RING

SETR16AI-TINEL-LOCK-RING

TE Internal Number: CZ3664-000

Product Highlights [View All](#)

- Tinel-Lock Ring
- Cable Entry Diameter = 25.40 mm
- Wire/Cable Size = 42 AWG
- DC Resistance (Max.) = 1 Ω
- Operating Temperature = -65 - 200 °C

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features	Configuration Features
Product Type Tinel-Lock Ring	Braid Single
Electrical Characteristics DC Resistance (Max.) (Ω) 1	Industry Standards RoHS/ELV Compliance ? RoHS compliant, ELV compliant Lead Free Solder Processes ? Not relevant for lead free process RoHS/ELV Compliance History Always was RoHS compliant
Termination Features Wire/Cable Size (AWG) 42	Environmental Operating Temperature (°C) -65 - +200
Dimensions Cable Entry Diameter (mm [in]) 25.40 [1.000]	Other Brand Raychem Node Classification Connector Backshells/Adapters
Body Features Material Nickel-Titanium Alloy	

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

