




TCFS-12-19B-015-25BW Product Details

 [Share](#)

 [Print](#)

 [Email](#)



TCFS-12-19B-015-25BW

TE Internal Number: D24198-000

 [Active](#)

Heat Shrinkable Cable Kits and Assemblies

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- Heat Shrinkable Cable Feedthrough
- Mount Type = Bulkhead Feedthrough
- Thread Size = M12 x 1.5
- Aluminum Alloy Feedthrough Material
- Cadmium Over Electroless Nickel Feedthrough Finish

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [Customer Drawing](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Heat Shrinkable Cable Feedthrough
- [Thread Size](#) = M12 x 1.5
- [Material](#) = Fluid Resistant Elastomer
- [Angle](#) = 90°
- Color = Olive Drab

Electrical Characteristics:

- Modification = None
- [Shielded](#) = No
- [Expanded ID, Min. \(mm \[in\]\)](#) = 11.00 [0.433]
- [Recovered ID, Max. \(mm \[in\]\)](#) = 5.60 [0.221]

Termination Features:

- [Adhesive](#) = S-1048 Holt Melt

Body Features:

- Mount Type = Bulkhead Feedthrough
- Feedthrough Material = Aluminum Alloy
- Feedthrough Finish = Cadmium Over Electroless Nickel
- [Feedthrough Type](#) = Single-sided
- Thread Length (mm [in]) = 15.00 [0.590]
- [Feedthrough Inner Diameter, Max. \(mm \[in\]\)](#) = 7.5 [3]
- A/F Body Diameter (mm [in]) = 24 [0.95]
- A/F Nut (mm [in]) = 17 [0.67]
- Length of Molded Part/Flange (mm [in]) = 43 [1.692]
- Hole Diameter (mm [in]) = 13.00 [0.512]

Configuration Features:

- [Material Code](#) = 25

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Other:

- Brand = Raychem

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference Products](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

