




+ RELAYS, CONTACTORS & SWITCHES
PUSHBUTTON SWITCHES



✓ Active

TE CONNECTIVITY (TE)
AV19 SPM 5A SPOT LED WHITE 12V
[Alcoswitch](#) | [Alcoswitch AV](#)

AV1910D112Q04
TE Internal Number: 2213765-1

- [EU RoHS Compliant](#)
- [EU ELV Compliant](#)
- Configuration (Pole-Throw)** Single Pole - Single Throw
- Number of Actuators** Single
- Actuator Profile** Flush
- Bushing Style** Threaded
- Illuminated** Yes

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings

ANTI-VANDAL SWITCH 19mm SPOT LED
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Agency Approvals

UL Report

Anti Vandal Switches

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Illuminated** Yes
- Actuator Style** Round
- Product Type** Switch
- Switch Type** Pushbutton
- Dust Proof** Yes

Configuration Features

- Configuration (Pole-Throw)** Single Pole - Single Throw
- Number of Actuators** Single
- Snap Action** Without
- Support Bracket** Without
- Tactile** No
- Operating Function** Momentary
- ESD Grounding Terminal** Without
- Detent Style** Audible

Electrical Characteristics

- Voltage Rating (VAC)** 250

Body Features

- Actuator Profile** Flush
- Bushing Style** Threaded
- Case Material** PBT

Contact Features

- Contact Current Rating (A)** 5
- Contact Plating** Silver

Termination Features

Termination Type Wire Lugs

Mechanical Attachment

Mounting Type Panel

Mounting Angle Vertical

Housing Features

Process Sealed Yes

Dimensions

Bushing Length (in) 19

Statement of Compliance

Statement of Compliance

PDF