




EUROCARD

TE Internal #: 1-1393644-6
Eurocard Connectors, Plug, Board-to-Board, 96 Position, .1 in [2.54 mm] Centerline, Printed Circuit Board, 3 Row, Right Angle, 32 Column

[View on TE.com >](#)

Connectors > PCB Connectors > Backplane Connectors > Eurocard Connectors



Connector & Housing Type: **Plug**
Connector System: **Board-to-Board**
Termination Post & Tail Length: **3 mm [.118 in]**
Number of Positions: **96**
Centerline (Pitch): **2.54 mm [.1 in]**

Features

Product Type Features

Connector & Housing Type	Plug
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
DIN Size	Standard
DIN Level	I

Configuration Features

Position Locations Loaded	Every even pitch
Number of Positions	96
Number of Rows	3
PCB Mount Orientation	Right Angle
Number of Columns	32
Number of Signal Positions	96
Rows Loaded	A, B, C



Contact Features

Contact Type	Pin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	1.5 A

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
Termination Post & Tail Length	3 mm[.118 in]

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Alignment	With
Panel Mount Feature	Without
PCB Mount Retention	With
PCB Mount Retention Type	Mounting Hole
Connector Mounting Type	Board Mount

Housing Features

Housing Material	Polyester - GF
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Connector Height	12.62 mm
PCB Thickness (Recommended)	1.6 mm[.063 in]
Row-to-Row Spacing	2.54 mm[.1 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Shielded	No
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tray
------------------	------

Product Compliance






For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 925486-1 MOD. IV SNAP-IN HSG 96 POS.	 TE Part # 1-148057-5 096 EURO TYP C RECP 13MM ASSY	 TE Part # 5535043-5 ASSY,RECEPTACLE,EUOCARD,TYPE	 TE Part # 5535089-5 ASSEMBLY,RECEPTACLE,EUOCARD, T
 TE Part # 650473-5 096 EURO TYPE C PIN ST ASSY	 TE Part # 5536412-4 ASSY,RECEPT,EURO,TYPE C,LEAD-FREE,96,18	 TE Part # 5148057-5 ASSY,RECEPTACLE,EUOCARD,TYPE C,LEAD-FRE	 TE Part # 5650473-5 ASSY,PIN,EUOCARD,TYPE C,LEAD-



 TE Part # 650947-5 096 EURO TYPE C PIN ST ASSY	 TE Part # 5535090-4 ASSEMBLY,RECEPTACLE,EUROCARD, T	 TE Part # 3-1393641-1 V42254B2202C960=PC612 FEDERLEI	 TE Part # 5148059-5 ASSY,RECEPTACLE,EUROCARD,TYPE C,LEAD-FRE
 TE Part # 5650963-4 ASSY,RECEPTACLE,EUROCARD,TYPE	 TE Part # 9-1393644-1 V42254B1200C960=PC612 MESSERLE	 TE Part # 5650461-4 ASSY,RECEPTACLE,EUROCARD,TYPE	 TE Part # 5535043-4 ASSY,RECEPTACLE,EUROCARD,TYPE
 TE Part # 5650895-4 ASSY,RECEPT,EUROCARD,TYPE R,LE	 TE Part # 5535090-5 ASSEMBLY,RECEPTACLE,EUROCARD, T	 TE Part # 5535032-5 ASSY,RECEPTACLE,EUROCARD,TYPE C,LEAD-FRE	 TE Part # 650913-5 096 EURO TYPE C PIN BL ASSY

Documents

Product Drawings

V42254B1100C960=PC612 MESSERLE

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-1393644-6_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1393644-6_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1393644-6_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Environmental Compliance



Product Compliance

English

Product Compliance

English