

1-1747066-3 ✓ ACTIVE




GRACE INERTIA 2.5

TE Internal #: 1-1747066-3

Rectangular Connector Housings, Wire-to-Board, 3 Position, .098 in [2.5 mm] Centerline, 1 Row, Nylon 66 GF, Plug, Socket, GRACE INERTIA 2.5

[View on TE.com >](#)

Connectors > Rectangular Connectors > Rectangular Connector Housings > STD Temp Sig GRACE INERTIA Plug



Connector System: **Wire-to-Board**

Number of Positions: **3**

Centerline (Pitch): **2.5 mm [.098 in]**

Number of Rows: **1**

Housing Material: **Nylon 66 GF**

[All STD Temp Sig GRACE INERTIA Plug \(63\)](#)

Features

Product Type Features

Connector System	Wire-to-Board
Connector & Housing Type	Plug
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Connector Type	Housing
Product Type	Connector

Configuration Features

Number of Cavities	3
Number of Positions	3
Number of Rows	1
Preloaded	No

Electrical Characteristics



Operating Voltage	50 VDC
-------------------	--------

Contact Features

Contact Layout	Inline
Multiple Contact Types	Without
Shunts/Shorting Bars	Without
Contact Type	Socket

Mechanical Attachment

Panel Mount	No
Panel Mount Feature	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	2.5 mm [.098 in]
Housing Material	Nylon 66 GF
Housing Color	Red

Dimensions

Height	11.3 mm [.445 in]
Length	9.6 mm [.378 in]
Width	7.1 mm [.279 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C [-22 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Assembly Integration Feature	Without
Halogen Free	No
Circuit Application	Signal
For Use With	Header

Identification Marking

Circuit Identification Feature	Without
--------------------------------	---------

Packaging Features

Packaging Quantity	800
Packaging Method	Bag

Product Compliance




[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-G7534A-C1701
STD Temp Sig GRACE INERTIA Cap



TE Part # CAT-G7534A-P729
STD Temp Sig GRACE INERTIA Plug



TE Part # 3-2232546-3
G12.5 HDR ASS 3P RED NO BOSS TAPE



TE Part # 1903392-1
GIC 2.5 W CAP HSG 3P NATURAL




TE Part # 3-2232701-4
NEW GI CONN2.5 PLUG HSG 3P YLW

Also in the Series | GRACE INERTIA 2.5



Connector Contacts(2)



PCB Headers & Receptacles(138)



PCB Latches, Locks & Retainers(5)



Rectangular Connector Housings(49)



Rectangular Connector Locking(2)



Rectangular Power Connectors(35)

Wire-to-Board Connector Assemblies
& Housings(72)

Wire-to-Board Connector Contacts(5)

Documents

Product Drawings

GRACE INERTIA CONN 2.5 PLUG HSG 3P RED

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1-1747066-3_E.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-1747066-3_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1747066-3_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

1-1747066-3

Rectangular Connector Housings, Wire-to-Board, 3 Position, .098 in [2.5 mm]
Centerline, 1 Row, Nylon 66 GF, Plug, Socket, GRACE INERTIA 2.5



Product Compliance

English