



Connectors > Power Connectors > Circular Power > Circular Power Connectors > Connectors with Posted Pin Contacts, CPC Series 1



Connector Product Type: **Connector Assembly**

Operating Voltage: **250 VDC**

Connector System: **Wire-to-Board, Wire-to-Panel**

Number of Positions: **16**

Sealable: **No**

[All Connectors with Posted Pin Contacts, CPC Series 1 \(39\)](#)

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Board, Wire-to-Panel
Sealable	No
Connector & Housing Type	Receptacle
Circular Connector Shell Type	All Plastic

Configuration Features

Number of Positions	16
Number of Power Positions	0
Keying	A
Number of Signal Positions	16

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Reverse Gender	No
Contact Type	Pin

Termination Features

--	--



Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

Mechanical Attachment

Panel Mount Feature Type	Flange with Mounting Holes
Connector Mounting Type	Panel Mount
Mating Alignment	With
Mating Retention	With
Panel Mount Feature	With
Mating Alignment Type	Keyed
Mating Retention Type	Threaded Coupling

Housing Features

Housing Color	Black
Housing Material	PA 6.6
Circular Connector Shell Size	17

Dimensions

Assembly Length	40 mm[1.575 in]
-----------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	None

Operation/Application

Circuit Application	Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tray
Packaging Quantity	24

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold




EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 207299-3 FLANGE PLUG MOUNT CPC	 TE Part # 206037-1 CPC PLUG ASSEMBLY SIZE 17-16	 TE Part # CAT-AM71-C83998B CPC Cable Clamps	 TE Part # 207241-1 CABLE BOOT, SZ 17, CPC
 TE Part # 207387-1 CABLE GRIP, SZ 17, CPC	 TE Part # 207387-2 CABLE GRIP, SZ 17, CPC	 TE Part # 4-2407269-1 CAP, CPC, SIZE 17 RECP, ORANGE	 TE Part # 4-2407269-4 CAP, CPC, SIZE 17 RECP, YELLOW





TE Part # 4-2407269-3
CAP, CPC, SIZE 17 RECP, RED



TE Part # 4-2407269-2
CAP, CPC, SIZE 17 RECP, BLACK



TE Part # 207303-3
CPC RECPT ASSEMBLY SIZE 17-16

TE Part # 1-207303-6
CPC RECPT ASSM SIZE 17-16

Also in the Series | AMP CPC



Circular Connector Adapters(7)



Circular Connector Boots & Strain Relief(6)




Circular Connector Caps & Covers(16)



Circular Connector Hardware(3)



Circular Connector Keying Plugs(2)



Circular Connector Seals(36)



Circular Power Connectors(467)



Insertion & Extraction Tools(1)



Power Contacts(6)



Sealing Sleeves(2)



Unscreened Circular Connector Backshells & Clamps(56)

Documents

Product Drawings
CPC RECPT ASSEMBLY SIZE 17-16

English

CAD Files
3D PDF
3D
Customer View Model



[ENG_CVM_CVM_1-207303-3_AE.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-207303-3_AE.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-207303-3_AE.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMP Circular Connectors for Commercial Signal & Power Applications](#)

English

Product Specifications

[Connector, Circular Plastic](#)

English

[Product Specification](#)

English

Product Environmental Compliance

[MD_1-207303-3_103020171030_dmtec](#)

English

[MD_1-207303-3_103020171030_dmtec](#)

English

Agency Approvals

[CSA Certificate](#)

English